

Specifications

Photo is representative

Eaton AHCL530C

Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 30A, Industrial, 125V, Back, Yellow, Black, Ultra grip, Nylon, L5-30, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

General specifications

PRODUCT NAME	Eaton Arrow Hart Color Coded Locking Connector
CATALOG NUMBER	AHCL530C
UPC	032664755811
PRODUCT LENGTH/DEPTH	2.23 in
PRODUCT HEIGHT	3.71 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Color Coded Locking



Powering Business Worldwide

Product specifications

SPECIAL FEATURES Voltage Color Coding

TYPE Locking Connector

AMPERAGE RATING 30A

VOLTAGE RATING 125 V

APPLICATION Industrial

WIRING METHOD Back

NUMBER OF WIRES 3

NUMBER OF POLES Two-pole

COLOR Yellow
Black

CORD DIAMETER 0.38-1 in (9.5-25.4 mm)

MATERIAL Nylon

OPERATING TEMPERATURE -40 to 60 °C (-40 to 140 °F)

ALLOWABLE WIRE SIZE #14-8 AWG

NEMA CONFIGURATION L5-30

TORQUE RATING 20 lbf-inch

DESIGN TYPE Ultra grip

FACE/BODY MATERIAL Nylon

Resources

MULTIMEDIA [Eaton Arrow Hart color coded locking devices](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - AHCL530C](#)

[Arrow Hart color coded industrial grade L5-30 locking devices spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton AHCL530C

Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 30A, Industrial, 125V, Back, Yellow, Black, Ultra grip, Nylon, L5-30, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

General specifications

PRODUCT NAME	Eaton Arrow Hart Color Coded Locking Connector
CATALOG NUMBER	AHCL530C
UPC	032664755811
PRODUCT LENGTH/DEPTH	2.23 in
PRODUCT HEIGHT	3.71 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Color Coded Locking



Powering Business Worldwide

Product specifications

SPECIAL FEATURES Voltage Color Coding

TYPE Locking Connector

AMPERAGE RATING 30A

VOLTAGE RATING 125 V

APPLICATION Industrial

WIRING METHOD Back

NUMBER OF WIRES 3

NUMBER OF POLES Two-pole

COLOR Yellow
Black

CORD DIAMETER 0.38-1 in (9.5-25.4 mm)

MATERIAL Nylon

OPERATING TEMPERATURE -40 to 60 °C (-40 to 140 °F)

ALLOWABLE WIRE SIZE #14-8 AWG

NEMA CONFIGURATION L5-30

TORQUE RATING 20 lbf-inch

DESIGN TYPE Ultra grip

FACE/BODY MATERIAL Nylon

Resources

MULTIMEDIA [Eaton Arrow Hart color coded locking devices](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - AHCL530C](#)

[Arrow Hart color coded industrial grade L5-30 locking devices spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

