# Specifications



Photo is representative





## Eaton C0150E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°c, 150 va

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Type MTE industrial control transformer |
| **CATALOG NUMBER** | C0150E2AFB |
| **UPC** | 786680420863 |
| **PRODUCT LENGTH/DEPTH** | 3.88 in |
| **PRODUCT HEIGHT** | 4.67 in |
| **PRODUCT WIDTH** | 3.75 in |
| **PRODUCT WEIGHT** | 5.3 lb |
| **WARRANTY** | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| **COMPLIANCES** | RoHS Compliant |
| **CERTIFICATIONS** | CSA Certified<br>UL Listed<br>cUL Certified |
| **CATALOG NOTES** | Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability |

Powering Business Worldwide

## Physical Attributes

| | |
|---|---|
| **COIL MATERIAL** | Copper windings |
| **DESIGN** | MTE |
| **TAP SIZE** | None |

## Performance Ratings

| | |
|---|---|
| **PRIMARY VOLTAGE** | 220 x 440 V, 230 x 460 V, 240 x 480 V |
| **TEMPERATURE RATING** | 55°C |
| **VOLT AMPERE RATING** | 150 VA |
| **SECONDARY VOLTAGE** | 120/115/110 V |

## Miscellaneous

| | |
|---|---|
| **MODIFICATION 1** | Factory-mounted two-pole primary fuse block for non-rejection type fuses |
| **SPECIAL FEATURES** | Primary fuse block |

## Resources

| | |
|---|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C0150E2AFB |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

# Specifications



Photo is representative





## Eaton C0150E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°c, 150 va

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Type MTE industrial control transformer |
| **CATALOG NUMBER** | C0150E2AFB |
| **UPC** | 786680420863 |
| **PRODUCT LENGTH/DEPTH** | 3.88 in |
| **PRODUCT HEIGHT** | 4.67 in |
| **PRODUCT WIDTH** | 3.75 in |
| **PRODUCT WEIGHT** | 5.3 lb |
| **WARRANTY** | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| **COMPLIANCES** | RoHS Compliant |
| **CERTIFICATIONS** | CSA Certified<br>UL Listed<br>cUL Certified |
| **CATALOG NOTES** | Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability |

Powering Business Worldwide

## Physical Attributes

| | |
|---|---|
| **COIL MATERIAL** | Copper windings |
| **DESIGN** | MTE |
| **TAP SIZE** | None |

## Performance Ratings

| | |
|---|---|
| **PRIMARY VOLTAGE** | 220 x 440 V, 230 x 460 V, 240 x 480 V |
| **TEMPERATURE RATING** | 55°C |
| **VOLT AMPERE RATING** | 150 VA |
| **SECONDARY VOLTAGE** | 120/115/110 V |

## Miscellaneous

| | |
|---|---|
| **MODIFICATION 1** | Factory-mounted two-pole primary fuse block for non-rejection type fuses |
| **SPECIAL FEATURES** | Primary fuse block |

## Resources

| | |
|---|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C0150E2AFB |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.