

Specifications



Photo is representative



Eaton C0200E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 200 va

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0200E2AFB
UPC	786680420887
PRODUCT LENGTH/DEPTH	4.18 in
PRODUCT HEIGHT	5.29 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	8.9 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes		Performance Ratings	
COIL MATERIAL	Copper windings	PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
DESIGN	MTE	TEMPERATURE RATING	55°C
TAP SIZE	None	VOLT AMPERE RATING	200 VA
		SECONDARY VOLTAGE	120/115/110 V
Miscellaneous		Resources	
MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses	SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0200E2AFB
SPECIAL FEATURES	Primary fuse block		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:

Specifications



Photo is representative



Eaton C0200E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 200 va

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0200E2AFB
UPC	786680420887
PRODUCT LENGTH/DEPTH	4.18 in
PRODUCT HEIGHT	5.29 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	8.9 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes		Performance Ratings	
COIL MATERIAL	Copper windings	PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
DESIGN	MTE	TEMPERATURE RATING	55°C
TAP SIZE	None	VOLT AMPERE RATING	200 VA
		SECONDARY VOLTAGE	120/115/110 V
Miscellaneous		Resources	
MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses	SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0200E2AFB
SPECIAL FEATURES	Primary fuse block		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

