



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## APS04 #410 Al Split Bolt Conn

*Nsi Industries*

Catalog Number	APS04
Manufacturer	Nsi Industries
Description	Aluminum Dual-Rated Split Bolt 10 Sol - 4 STR Aluminum Dual-Rated Split Bolts Are Made From Tin-Plated Aluminum. UL-486B Listed For Aluminum and Copper Conductor Combinations.
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum Alloy-Tin Plated
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	10 SOL-4 STR
Wire Type	Class A & B

### Material, Color, and Finish

Color	Aluminum
Finish	Aluminum

### Dimensions and Weight

Size	L=1.380 - W=.620
------	------------------

### Descriptions

Description	#410 AL SPLIT BOLT CONN
extra long description	NSI APS04 Aluminum Split Bolt 4
Features	Aluminum Dual-Rated Split Bolt 10 SOL - 4 STR Aluminum Dual-Rated Split bolts are made from tin-plated aluminum. UL-486B listed for aluminum and copper conductor combinations.
Long Description	Aluminum Dual-Rated Split Bolt 10 SOL - 4 STR Aluminum Dual-Rated Split bolts are made from tin-plated aluminum. UL-486B listed for aluminum and copper conductor combinations.
Product Type	Aluminum Split Bolt 4
Special Features	10 SOL-4 STR - 75 Pack

### Manufacturer Information

Brand	NSi
GTIN	00662381020512
Manufacturers Part Number	APS04
UPC	662381020512



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS

Type ..... Aluminum Split Bolts

## Packaging

Carton ..... 1

Package ..... 75

Weight Per each ..... 0.06

## Uses, Certifications, and Standards

Application ..... Wire Termination

environmental conditions ..... 90 C

standard ..... UL486B

Temperature Rating ..... 90 C