



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ATQ610 500V 6/10A TD Midget Fuse

Mersen Fuses

Catalog Number	ATQ610
Manufacturer	Mersen Fuses
Description	Fuse Atq - Midget - Time-Delay 500VAC 0.6A Ferrule Amp-Trap®
Weight per unit	0.0120 (lbs/each)
Product Category	Small Dimension Fuses

Features

AC Voltage Rating	500
amperage rating	0.6
class	Midget
connection	Ferrule
Fuse Class	Midget
interrupt rating	10
Voltage Rating	500

Material, Color, and Finish

Body Material	GMG
---------------	-----

Dimensions and Weight

Size	1.5 x 0.41
------	------------

Descriptions

Description	500V 6/10A TD MIDGET FUSE
extra long description	Mersen ATQ6/10 Fuse ATQ - Midget -
Features	Amp-Trap ATQ midget time-delay fuses are rated 500VAC with 42 ampere ratings from 1/10 to 30A. They are an excellent choice for supplemental protection of circuits where the available short circuit current does not exceed 10,000A. (Not for Branch Circuit Protection)
Long Description	Fuse ATQ - Midget - Time-Delay 500VAC 0.6A Ferrule Amp-Trap®
Product Type	Sicherungseinsatz Atq – Miniatur – Träge 500VAC 0.6A Kapsels
Short Description	500V 6/10A TD MIDGET FUSE
Special Features	Numerous ratings for a wide variety of applications up to 500VAC Time-delay (12 seconds at 200 percent rating) for circuits with high inrush current Can be used with UltraSafe™ Fuse holders 1 1/2" x 13/32" (10 mm x 38 mm) dimensions



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Mersen
GTIN	00782001902674
Manufacturers Part Number	ATQ6/10
UPC	782001902674

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	Midget Fuses

Packaging

Carton	1
Package	10
Weight Per each	0.012

Uses, Certifications, and Standards

Application	Supplemental protection of lighting, solenoid, motor and transformer circuits
Mounting standard	Clip UL listed to standard 248-14 File E33925 CSA Certified to Standard C22.2 No. 248.14