



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C0300E5E 300 Va Type Mte Control Transformer

Eaton Corp

Catalog Number	C0300E5E
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 200/220/440V, 208/230/460V, 240/480V, Taps: None, SV: 23/110V, 24/115V, 25/120V, 55°C, 300 Va , Cu Magnet Wire
Weight per unit	17.5 (lbs/each)
Product Category	Encapsulated Industrial Contro

### Features

dimensions	5.1180 IN X 5.2360 IN X 4.7640 IN
kva rating	300 VA
Primary Voltage	200/220/440 V, 208/230/460 V, 240/480 V
Secondary Voltage	23/110 V, 24/115 V, 25/120 V
Tap Size	NONE

### Descriptions

Description	300 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0300E5E 300 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 300 va , cu magnet wire
Product Type	300 Va Type Mte Control Transformer

### Manufacturer Information

Brand	Eaton
GTIN	00786680420429
Manufacturers Part Number	C0300E5E
UPC	786680420429

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	17.5

## Uses, Certifications, and Standards

Application	Other
standard	UL Listed,cUL Certified,CSA Certified,RoHS Compliant
Temperature Rating	55°C