

Eaton C0350E2AFB

Catalog Number: C0350E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°c, 350 va



Photo is representative

General specifications

Product Name

Eaton Type MTE industrial control transformer

Catalog Number

C0350E2AFB

UPC

786680420948

Product Length/Depth

4.56 in

Product Height

5.29 in

Product Width

4.5 in

Product Weight

11.6 lb

Warranty

Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed
CSA Certified
cUL Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

220 x 440 V, 230 x 460 V, 240 x 480 V

Temperature rating

55°C

Volt ampere rating

350 VA

Secondary voltage

120/115/110 V

Miscellaneous

Modification 1

Factory-mounted two-pole primary fuse block for non-rejection type fuses

Special features

Primary fuse block

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0350E2AFB](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C0350E2AFB

Catalog Number: C0350E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°c, 350 va



Photo is representative

General specifications

Product Name

Eaton Type MTE industrial control transformer

Catalog Number

C0350E2AFB

UPC

786680420948

Product Length/Depth

4.56 in

Product Height

5.29 in

Product Width

4.5 in

Product Weight

11.6 lb

Warranty

Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed
CSA Certified
cUL Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

220 x 440 V, 230 x 460 V, 240 x 480 V

Temperature rating

55°C

Volt ampere rating

350 VA

Secondary voltage

120/115/110 V

Miscellaneous

Modification 1

Factory-mounted two-pole primary fuse block for non-rejection type fuses

Special features

Primary fuse block

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0350E2AFB](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)