



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DNF240B Open N-R 2P 40A DP Cont Box Lugs W/QC Term 240vac *Eaton Corp*

Catalog Number	C25DNF240B
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 40A, 208-240 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 40A, Contactor, 2P, 50A, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Coil Voltage	50/60 Hz
Enclosure Type	Open with metal mounting plate

Dimensions and Weight

Depth	3.35
Height	3.75
Width	2.4

Descriptions

Description	OPEN N-R 2P 40A DP CONT BOX LUGS W/QC TERM 240VAC
extra long description	ETN C25DNF240B OP N-R 2P 40ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 40A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, 2P, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing
Product Type	Op N-R 2P 40ADPCNT BXLGS W/Qc240ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300402
Manufacturers Part Number	C25DNF240B
UPC	782116300402

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.19

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Recognized, CSA Certified, RoHS Compliant