

Specifications



Photo is representative



Eaton C0050E3AFB

Eaton Type MTE industrial control transformer, pv: 208/277v, taps: none, sv: 120v, 55°C, 50 va, cu magnet wire

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0050E3AFB
UPC	786680550508
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	4.04 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	2.8 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cUL Certified UL Listed CSA Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes	
COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings	
PRIMARY VOLTAGE	208/277 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	50 VA
SECONDARY VOLTAGE	120 V

Miscellaneous	
MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0050E3AFB
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton C0050E3AFB

Eaton Type MTE industrial control transformer, pv: 208/277v, taps: none, sv: 120v, 55°C, 50 va, cu magnet wire

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0050E3AFB
UPC	786680550508
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	4.04 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	2.8 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cUL Certified UL Listed CSA Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes	
COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings	
PRIMARY VOLTAGE	208/277 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	50 VA
SECONDARY VOLTAGE	120 V

Miscellaneous	
MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0050E3AFB
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

