

Specifications



Photo is representative



Eaton C0200E1B

Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none, sv: 24v, 55°c, 200 va

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0200E1B
UPC	786680423000
PRODUCT LENGTH/DEPTH	5.5 in
PRODUCT HEIGHT	7.5 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	7.7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified UL Listed cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in

Specifications



Photo is representative



Eaton C0200E1B

Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none, sv: 24v, 55°c, 200 va

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0200E1B
UPC	786680423000
PRODUCT LENGTH/DEPTH	5.5 in
PRODUCT HEIGHT	7.5 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	7.7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified UL Listed cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in