

# Specifications



Photo is representative

## Eaton CDR1034

Eaton Crouse-Hinds series PowerMate CDR receptacle, 100A, Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR1034
UPC	662276276895
PRODUCT LENGTH/DEPTH	5.25 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	2.2 lb



### Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

### Product specifications

AMPERAGE RATING	100A
-----------------	------

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Three-wire, four-pole
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds CDR1034 3D drawing](#)

**BROCHURES** [PowerMate Drilling Pin and Sleeve Devices brochure](#)

**CATALOGS** [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

**CERTIFICATION REPORTS** [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

**INSTALLATION INSTRUCTIONS** [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - CDR1034](#)  
[PowerMate Connectors](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.



# Specifications



Photo is representative

## Eaton CDR1034

Eaton Crouse-Hinds series PowerMate CDR receptacle, 100A, Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR1034
UPC	662276276895
PRODUCT LENGTH/DEPTH	5.25 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	2.2 lb



### Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

### Product specifications

AMPERAGE RATING	100A
-----------------	------

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Three-wire, four-pole
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds CDR1034 3D drawing](#)

**BROCHURES** [PowerMate Drilling Pin and Sleeve Devices brochure](#)

**CATALOGS** [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

**CERTIFICATION REPORTS** [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

**INSTALLATION INSTRUCTIONS** [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - CDR1034](#)  
[PowerMate Connectors](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.

