

# Specifications



Photo is representative



## Eaton C0200E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 200 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0200E2AFB
<b>UPC</b>	786680420887
<b>PRODUCT LENGTH/DEPTH</b>	4.18 in
<b>PRODUCT HEIGHT</b>	5.29 in
<b>PRODUCT WIDTH</b>	4.5 in
<b>PRODUCT WEIGHT</b>	8.9 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

## Miscellaneous

MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

## Performance Ratings

PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	200 VA
SECONDARY VOLTAGE	120/115/110 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0200E2AFB</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

