

Specifications

Photo is representative



Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

Product specifications

SPECIAL FEATURES	Provision only
TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single-phase
WIRE SIZE	#6-4/0 AWG
BOX SIZE	E
ENCLOSURE	NEMA 1
INTERRUPT RATING	25 kAIC

General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC24L125E
UPC	782116200146
PRODUCT LENGTH/DEPTH	32 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	7 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

Powering Business Worldwide