

Specifications



Photo is representative



Eaton CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHM1N7N7NSU
UPC	786685404264
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	31 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	30 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231



Powering Business Worldwide

Physical Attributes	
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
FEED TYPE	Bottom
MOUNTING	Surface
NUMBER OF CIRCUITS	4
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
TYPE	Metered-ring

Resources	
CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHM1N7N7NSU

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHM1N7N7NSU
UPC	786685404264
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	31 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	30 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231



Powering Business Worldwide

Physical Attributes	
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
FEED TYPE	Bottom
MOUNTING	Surface
NUMBER OF CIRCUITS	4
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
TYPE	Metered-ring

Resources	
CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHM1N7N7NSU

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

