



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue  
76711-0000, TX Waco  
Phone: 254-752-3331  
Fax: 254-752-3460



## **C25DNF240B Open N-R 2P 40A DP Cont Box Lugs W/QC Term 240vac** *Eaton Corp*

Catalog Number	C25DNF240B
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 40A, 208-240 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 40A, Contactor, 2P, 50A, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### **Features**

Coil Voltage	50/60 Hz
Enclosure Type	Open with metal mounting plate

### **Dimensions and Weight**

Depth	3.35
Height	3.75
Width	2.4

### **Descriptions**

Description	OPEN N-R 2P 40A DP CONT BOX LUGS W/QC TERM 240VAC
extra long description	ETN C25DNF240B OP N-R 2P 40ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 40A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, 2P, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing
Product Type	Op N-R 2P 40ADPCNT BXLGS W/Qc240ac

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00782116300402
Manufacturers Part Number	C25DNF240B
UPC	782116300402

### **Taxonomies, Classifications, and Categories**

Category Description	DP CONTACTORS
Type	Definite purpose contactor



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue  
76711-0000, TX Waco  
Phone: 254-752-3331  
Fax: 254-752-3460

## Packaging

Carton	1
Weight Per each	1.19

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Recognized, CSA Certified, RoHS Compliant