

# Specifications



Photo is representative



## Eaton CHP32L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 64, 32, Three-wire, Single-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CHP32L150R
<b>UPC</b>	786689058692
<b>PRODUCT LENGTH/DEPTH</b>	29 in
<b>PRODUCT HEIGHT</b>	5.19 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

## Product specifications

**SPECIAL FEATURES** Cover included

**TYPE** Main Lug Only

**AMPERAGE RATING** 150 A

**BUS MATERIAL** Copper

**FEED TYPE** Overhead

**NUMBER OF CIRCUITS** 64

**NUMBER OF SPACES** 32

**PHASE** Single-phase

**BOX SIZE** X5

**ENCLOSURE** NEMA 3R

**ENCLOSURE MATERIAL** Metallic

**INTERRUPT RATING** 25 kAIC

**NUMBER OF WIRES** 3

## Resources

**MULTIMEDIA** [AFCI Educational Video](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - CHP32L150R](#)

**WARRANTY GUIDES** [Eaton type CH circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton CHP32L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 64, 32, Three-wire, Single-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CHP32L150R
<b>UPC</b>	786689058692
<b>PRODUCT LENGTH/DEPTH</b>	29 in
<b>PRODUCT HEIGHT</b>	5.19 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

## Product specifications

**SPECIAL FEATURES** Cover included

**TYPE** Main Lug Only

**AMPERAGE RATING** 150 A

**BUS MATERIAL** Copper

**FEED TYPE** Overhead

**NUMBER OF CIRCUITS** 64

**NUMBER OF SPACES** 32

**PHASE** Single-phase

**BOX SIZE** X5

**ENCLOSURE** NEMA 3R

**ENCLOSURE MATERIAL** Metallic

**INTERRUPT RATING** 25 kAIC

**NUMBER OF WIRES** 3

## Resources

**MULTIMEDIA** [AFCI Educational Video](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - CHP32L150R](#)

**WARRANTY GUIDES** [Eaton type CH circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

