

Specifications

Photo is representative

Eaton CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V

Product specifications

| | |
|-----------------------------|------------------|
| SPECIAL FEATURES | Standard |
| TYPE | Main breaker |
| AMPERAGE RATING | 200 A |
| BUS MATERIAL | Copper |
| MAIN CIRCUIT BREAKER | CSR |
| NUMBER OF CIRCUITS | 42 |
| NUMBER OF SPACES | 42 |
| PHASE | Single-phase |
| WIRE SIZE | #2 AWG-300 kcmil |
| FEED TYPE | Overhead |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | K |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 25 kAIC |
| NUMBER OF WIRES | 3 |

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton CH main breaker loadcenter |
| CATALOG NUMBER | CH42B200R |
| UPC | 782113098227 |
| PRODUCT LENGTH/DEPTH | 37 in |
| PRODUCT HEIGHT | 5.19 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 15.5 lb |
| WARRANTY | Limited lifetime |
| CERTIFICATIONS | UL 67 UL 50 |
| CATALOG NOTES | Furnished with hub closure plates. Loadcenter contains single insulated/bondable neutral. |

