

Specifications

Photo is representative



Eaton CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CHP24L150R
UPC	786689058623
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

SPECIAL FEATURES	Cover included
TYPE	Main Lug
AMPERAGE RATING	150
BUS MATERIAL	Copper
FEED TYPE	Overhead
NUMBER OF CIRCUITS	48
NUMBER OF SPACES	24
PHASE	Single phase
BOX SIZE	X5
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25
NUMBER OF WIRES	3



Specifications

Photo is representative



Eaton CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CHP24L150R
UPC	786689058623
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

SPECIAL FEATURES	Cover included
TYPE	Main Lug
AMPERAGE RATING	150
BUS MATERIAL	Copper
FEED TYPE	Overhead
NUMBER OF CIRCUITS	48
NUMBER OF SPACES	24
PHASE	Single phase
BOX SIZE	X5
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25
NUMBER OF WIRES	3

