

DESCRIPTION

The CSL LED striplight brings together an economical price point and high performance available in 4ft and 8ft lengths.

FEATURES

- 4,000 and 8,000 nominal lumens
- 54,000 hour LEDs at L70 for reduced maintenance
- Up to 112 lumens per watt
- Choice of two color temperatures
- 0-10V dimming, standard
- Fully assembled for quick installation
- Frosted acrylic lens
- Wide range of applications
- Surface mount on wall or ceiling
- Universal voltage (120-277V)
- 80+ CRI
- DesignLights Consortium® (DLC) qualified; see www.designlights.org



tradeSELECT™



STANDARDS, CERTIFICATION AND COMPLIANCE

All luminaires are built to UL1598 standards and bear appropriate UL labels. Damp location label standard. DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.


WARRANTY

Five year warranty. Terms and conditions apply.


ORDERING GUIDE

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
CSL4-4035	4ft LED Striplight, 4,000 Lumens, 3500K, 0-10V dimming	4231	40.2	105	120
CSL4-4040	4ft LED Striplight, 4,000 Lumens, 4000K, 0-10V dimming	4517	40.2	112	120
CSL8-8035	8ft LED Striplight, 8,000 Lumens, 3500K, 0-10V dimming	8460	80.5	105	120
CSL8-8040	8ft LED Striplight, 8,000 Lumens, 4000K, 0-10V dimming	9036	80.5	112	120

DIMENSIONS




A - 7/8" Diameter Knockout
B - 5/32" x 1/4" Hole




Accessories (Order Separately)

GLH5 5' adjustable cable for suspension mount



A - 7/8" Diameter Knockout
B - 5/32" x 1/4" Hole



PHOTOMETRIC DATA

Test #17614 Test Date 2/15/2017

LUMINAIRE DATA

Luminaire	CSL4-4035 tradeSELECT® CSL, Striplight 48" x 2.25" LED striplight with opal lens
Ballast	SL38-1900
Ballast Factor	1.00
Lamp	LED
Fixture Lumens	4231
Watts	40.24
Mounting	Recessed
Shielding Angle	0° = 90 90° = 90
Spacing Criterion	0° = 1.25 90° = 1.26
Luminous Opening in Feet	Length: 4.00 Width: 0.17 Height: 0.08


ZONAL LUMEN SUMMARY

Zone	Lumens	% Lamp	% Fixt.
0-30	935	22.1	22.1
0-40	1536	36.3	36.3
0-60	2768	65.4	65.4
0-90	3902	92.2	92.2
0-180	4231	100.0	100.0

ENERGY DATA

Total Luminaire Efficiency	100.0%
Total Lumens per Watt	105
IESNA RP-1-2004 Compliance	Non-Compliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$2.26 based on 3000 hrs. and \$0.08 per KWH

INDOOR CANDELA PLOT



PHOTOMETRIC DATA

Test #17615 Test Date 2/15/2017

LUMINAIRE DATA

Luminaire	CSL4-4040 tradeSELECT® CSL, Striplight 48" x 2.25" LED striplight with opal lens
Ballast	SL38-1900
Ballast Factor	1.00
Lamp	LED
Fixture Lumens	4517
Watts	40.24
Mounting	Recessed
Shielding Angle	0° = 90 90° = 90
Spacing Criterion	0° = 1.25 90° = 1.26
Luminous Opening in Feet	Length: 4.00 Width: 0.17 Height: 0.08


ZONAL LUMEN SUMMARY

Zone	Lumens	% Lamp	% Fixt.
0-30	998	22.1	22.1
0-40	1641	36.3	36.3
0-60	2957	65.5	65.5
0-90	4167	92.2	92.2
0-180	4517	100.0	100.0

ENERGY DATA

Total Luminaire Efficiency	100.0%
Total Lumens per Watt	112
IESNA RP-1-2004 Compliance	Non-Compliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$2.12 based on 3000 hrs. and \$0.08 per KWH

INDOOR CANDELA PLOT



DESCRIPTION

The CSL LED striplight brings together an economical price point and high performance available in 4ft and 8ft lengths.



tradeSELECT™



FEATURES

- 4,000 and 8,000 nominal lumens
- 54,000 hour LEDs at L70 for reduced maintenance
- Up to 112 lumens per watt
- Choice of two color temperatures
- 0-10V dimming, standard
- Fully assembled for quick installation
- Frosted acrylic lens
- Wide range of applications
- Surface mount on wall or ceiling
- Universal voltage (120-277V)
- 80+ CRI
- DesignLights Consortium® (DLC) qualified; see www.designlights.org

STANDARDS, CERTIFICATION AND COMPLIANCE

All luminaires are built to UL1598 standards and bear appropriate UL labels. Damp location label standard. DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.


WARRANTY

Five year warranty. Terms and conditions apply.


ORDERING GUIDE

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
CSL4-4035	4ft LED Striplight, 4,000 Lumens, 3500K, 0-10V dimming	4231	40.2	105	120
CSL4-4040	4ft LED Striplight, 4,000 Lumens, 4000K, 0-10V dimming	4517	40.2	112	120
CSL8-8035	8ft LED Striplight, 8,000 Lumens, 3500K, 0-10V dimming	8460	80.5	105	120
CSL8-8040	8ft LED Striplight, 8,000 Lumens, 4000K, 0-10V dimming	9036	80.5	112	120

DIMENSIONS




A - 7/8" Diameter Knockout
B - 5/32" x 1/4" Hole




Accessories (Order Separately)

- GLH5** 5' adjustable cable for suspension mount



A - 7/8" Diameter Knockout
B - 5/32" x 1/4" Hole



PHOTOMETRIC DATA

Test #17614 Test Date 2/15/2017

LUMINAIRE DATA

Luminaire	CSL4-4035 tradeSELECT® CSL, Striplight 48" x 2.25" LED striplight with opal lens
Ballast	SL38-1900
Ballast Factor	1.00
Lamp	LED
Fixture Lumens	4231
Watts	40.24
Mounting	Recessed
Shielding Angle	0° = 90 90° = 90
Spacing Criterion	0° = 1.25 90° = 1.26
Luminous Opening in Feet	Length: 4.00 Width: 0.17 Height: 0.08


ZONAL LUMEN SUMMARY

Zone	Lumens	% Lamp	% Fixt.
0-30	935	22.1	22.1
0-40	1536	36.3	36.3
0-60	2768	65.4	65.4
0-90	3902	92.2	92.2
0-180	4231	100.0	100.0

ENERGY DATA

Total Luminaire Efficiency	100.0%
Total Lumens per Watt	105
IESNA RP-1-2004 Compliance	Non-Compliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$2.26 based on 3000 hrs. and \$0.08 per KWH

INDOOR CANDELA PLOT



PHOTOMETRIC DATA

Test #17615 Test Date 2/15/2017

LUMINAIRE DATA

Luminaire	CSL4-4040 tradeSELECT® CSL, Striplight 48" x 2.25" LED striplight with opal lens
Ballast	SL38-1900
Ballast Factor	1.00
Lamp	LED
Fixture Lumens	4517
Watts	40.24
Mounting	Recessed
Shielding Angle	0° = 90 90° = 90
Spacing Criterion	0° = 1.25 90° = 1.26
Luminous Opening in Feet	Length: 4.00 Width: 0.17 Height: 0.08

ZONAL LUMEN SUMMARY

Zone	Lumens	% Lamp	% Fixt.
0-30	998	22.1	22.1
0-40	1641	36.3	36.3
0-60	2957	65.5	65.5
0-90	4167	92.2	92.2
0-180	4517	100.0	100.0

ENERGY DATA

Total Luminaire Efficiency	100.0%
Total Lumens per Watt	112
IESNA RP-1-2004 Compliance	Non-Compliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$2.12 based on 3000 hrs. and \$0.08 per KWH

INDOOR CANDELA PLOT

