

Eaton CHP32L150R

Catalog Number: CHP32L150R

Eaton CH main lug loadcenters,Cover included,Main Lug Only,150A,X5,Copper,NEMA 3R,Metallic,Overhead,64,32,Three-wire,Single-phase



Photo is representative

General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CHP32L150R

UPC

786689058692

Product Length/Depth

29 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

26 lb

Warranty

Limited lifetime

Certifications

UL 67

UL 50

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

Special features

Cover included

Type

Main Lug Only

Amperage Rating

150 A

Bus material

Copper

Feed type

Overhead

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32L150R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHP32L150R

Catalog Number: CHP32L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 64, 32, Three-wire, Single-phase



Photo is representative

General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CHP32L150R

UPC

786689058692

Product Length/Depth

29 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

26 lb

Warranty

Limited lifetime

Certifications

UL 67

UL 50

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

Special features

Cover included

Type

Main Lug Only

Amperage Rating

150 A

Bus material

Copper

Feed type

Overhead

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32L150R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)