

# Specifications

## Eaton CHU6G6G5GS

Eaton pedestal mount unmetered, 20A, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2, NEMA 6-20R2, 3, 125V, 250V



### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU6G6G5GS
<b>UPC</b>	782114203927
<b>PRODUCT LENGTH/DEPTH</b>	4.3 in
<b>PRODUCT HEIGHT</b>	17.1 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	16.25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Unmetered
<b>CIRCUIT BREAKER POSITION 1</b>	Ground fault
<b>CIRCUIT BREAKER POSITION 2</b>	Ground fault
<b>CIRCUIT BREAKER POSITION 3</b>	Ground fault
<b>RECEPTACLE CENTER</b>	NEMA 5-20R2
<b>RECEPTACLE LEFT</b>	NEMA 5-20R2
<b>RECEPTACLE RIGHT</b>	NEMA 6-20R2
<b>FEED TYPE</b>	Top
<b>MOUNTING</b>	Surface
<b>NUMBER OF CIRCUITS</b>	4

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHU6G6G5GS</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton CHU6G6G5GS

Eaton pedestal mount unmetered, 20A, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2, NEMA 6-20R2, 3, 125V, 250V



### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU6G6G5GS
<b>UPC</b>	782114203927
<b>PRODUCT LENGTH/DEPTH</b>	4.3 in
<b>PRODUCT HEIGHT</b>	17.1 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	16.25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Unmetered
<b>CIRCUIT BREAKER POSITION 1</b>	Ground fault
<b>CIRCUIT BREAKER POSITION 2</b>	Ground fault
<b>CIRCUIT BREAKER POSITION 3</b>	Ground fault
<b>RECEPTACLE CENTER</b>	NEMA 5-20R2
<b>RECEPTACLE LEFT</b>	NEMA 5-20R2
<b>RECEPTACLE RIGHT</b>	NEMA 6-20R2
<b>FEED TYPE</b>	Top
<b>MOUNTING</b>	Surface
<b>NUMBER OF CIRCUITS</b>	4

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHU6G6G5GS</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

