# UL/CSA LISTED









# FAN & FIXTURE BOXES

FOR A VARIETY OF USES



# Choose the Fan or Fixture Box that's right for you...

# ...in Steel or Plastic – or a Combination!


No matter what your needs - or installation preferences, Arlington has a fan/fixture box to fit.

We manufacture a variety of steel and non-metallic boxes in many depths and

**Center screw** 

screws into joist

cubic inch capacities that install directly to the joist(s) for an extrasecure installation.



the bottom of a joist deliver a safe, secure an/Fixture bracket installation because both

the box and the bracket install directly to the joist!

Plus, we have a box for every ceiling condition!

**Joist** Mount

page

FBS405, FBS405T 6.0 cubic inches

**FBS407, FBS407T** 8.0 cubic inches



for NEW CONSTRUCTION



FB405

6.0 cubic inches



FB412 14.4 cubic inches



**Joist** Mount



Each of our boxes is UL Listed to hold fans and fixtures of a specific weight; generally from 35 to 200 lbs., depending on the box. In addition, our nonmetallic boxes offer a 2-hour fire rating.





**Under-Joist** Mount

page

**FBS415** 

1-1/2" depth 14.6 cubic inches

**FBS420** 2" depth 20.0 cubic inches

**For NEW** CONSTRUCTION



FB415

FB442

FB443

10.3 cubic inches

FB423 19.5 cubic inches

FB426 16.0 cubic inches



**Press Hold Joist Mount** 

For ceilings up to 1-1/2" thck.

**Applications include:** 

■ 1/2" or 5/8" drywal

■ Double drywall

■ Drywall mounted to hat channel, or furring strips then to the joist

■ Single or double joists

**Side Mount** 

page

page

**FBS415S** 1-1/2" depth

14.6 cubic inches **FBS420S** 

2" depth 20.0 cubic inches

FBS1423 23.0 cubic inches **For NEW** CONSTRUCTION

For NEW and Existing CONSTRUCTION



FB444 25.6 cubic inches

17.96 cubic inches

13.4 cubic inches



**Side Mount** 

**Side Mount** 

**Plastic Box** 

**Mounts** Between **Joists Adjustable Brackets** 

pages

**For NEW** CONSTRUCTION FBRS415 15.6 cubic

**For RETROFIT** 

FBRS407R 8.0 cubic inches

inches

FBRS420R 2" depth 20.0 cubic inches



**FB417S** 20.0 cubic inches



6.1 cubic inches

MB8

with Steel **Bracket** 

page

**NM** cable connector, mud cover in place and captive installation screws for both the box and the fan/fixture mounting

Most of Arlington's fan

boxes ship with an installed

8" Mounting **Block** 

**Arlington** 

For Any Suspended **Ceiling Frame** 

page

FBRS420SC, FS420SCL

2" depth 20.0 cubic inches



Arlington's fan/fixture boxes are patented

bracket.

Steel Boxes – Joist Mount

Steel Boxes – Joist Mount

#### **FBS405**

for 1/2" and 5/8" drywall

#### **FBS407**

for 5/8" drywall

Designed for 1/2" or 5/8" drywall ceilings, our cost-effective, plated steel FBS405 and FBS407 pan boxes mount directly to a ceiling joist for a super-secure installation.

- **For NEW CONSTRUCTION**
- UL Rated for 70 lb. fans; 200 lb. fixtures
- CSA Rated for 50 lb. fan or fixture




Item #	UPC/DCI/NAED MFG #01 899	Cubic Inches	Ceiling Thickness	Unit/Std Pkg
FBS405	76185	6.0	1/2", 5/8"	25
FBS407	76187	8.0	5/8"	25
* FBS405T	40500	6.0	1/2", 5/8"	25
* FBS407T	40700	8.0	5/8"	25

\* with threaded openings and #10 screws (supplied) for mounting fan/fixture bracket.





1 Secure installation! Box mounts directly to joist with captive screw near center.



Convenient. Drill (2) 1/8" dia. holes into joist through elongated openings on each side of box. Remove the (2) screws noted above. Use to mount the bracket...




Easy. Mount bracket into the holes with the (2) long screws removed previously. Mount fan/fixture per manufacturer's instructions.

Most of Arlington's Fan/Fixture boxes ship with an installed NM cable connector and mud cover – As well as captive installation screws for the box and bracket.

No parts to lose or misplace... they ship ready to use!

#### **Mount Under Joist**



NO LOOSE PARTS! Box and bracket installation screws ship captive, and stay in place until you're ready to use them.



1 Install FBS415/FBS420 box under the joist using the captive screws from the break-off tab.

Item #	UPC/DCI/NAED	Cubic	Under Joist	Unit/Std
	MFG #01 899	Inches	Box Depth	Pkg
FBS415	75204	14.6	1-1/2"	25
FBS420	75200	20.0	2"	25

#### FBS415

1-1/2" deep steel box

#### FBS420

#### 2" deep steel box


Arlington's octagonal steel boxes mount directly to a joist for a strong, safe fan or fixture installation. Available in two depths (1-1/2" and 2"), and two styles.

Combination hex/Phillips head screws provide easy installation with power screwdrivers.

FBS415 and FBS420 mount securely UNDER the joist.

- UL Rated for fans/fixtures up to 70 lbs.
- CSA Rated for 50 lb. fan or fixture

#### **Side Mount**



NO LOOSE PARTS! Box and bracket installation screws ship captive, and stay in place until you're ready to use them.

Bracket installationscrews

Item #	UPC/DCI/NAED	Cubic	Side Mount	Unit/Std	
	MFG #01 899	Inches	Box Depth	Pkg	
FBS415S	75206	14.6	1-1/2"	25	
FBS420S	75202	20.0	2"	25	

#### FBS415S

1-1/2" deep steel box

#### **FBS420S**

2" deep steel box

FBS415S and FBS420S mount on the SIDE of the joist.

Below installer removes captive screws in preparation for installing box to side of joist.



- UL Rated for fans/fixtures up to 70 lbs.
- CSA Rated for 50 lb. fan or fixture



1 Install FBS415S/FBS420S box on the side of the joist using the (4) captive screws removed from the break-off tab.



OPTION: Remove break-off tab with pliers.



3 Remove the bracket installation screws noted above. Use them to mount fan/fixture bracket to the box.




#### **FBRS415**

#### for New Construction

Arlington's super heavy-duty, plated steel fan/fixture boxes, with fully adjustable mounting brackets, are the innovative alternative to existing bar hanger brackets. Their heavy-duty construction eliminates fan wobble.

Plus, FBRS415 for new construction and FBRS420R, FBRS407R for retrofit, ship ready to use, with all mounting hardware secured in the assembly. There are no bagged parts or pieces to lose.

- For ceilings up to 1-1/4"
- Mounts easily, securely between joists 16" to 24" on-center (o.c.)
- Versatile 16" to 24" o.c. positioning between joists
- 15.6 cubic inch
- UL Rated: Fans/fixtures: up to 70 lbs. at 24" o.c. up to 110 lbs. at 16" o.c.
- CSA: Fans/fixtures up to 50 lbs.
- Competitively priced!





"Tooth" holds bracket temporarily in place.



Adjust box position from 16" to 24" o.c. between joists.



Remove screws from both ends of bracket.
Use them to attach bracket to joists.



4 Install fan mounting bracket.




CONVENIENT. Tab positions box flush on 1/2" ceiling. Fits ceilings up to 1-1/4" thick. Bracket is scored for ease of installation.



FLEXIBLE. For flush ceiling installations on ceilings over 1/2" thick, bend the bracket along the scoreline that matches the ceiling depth.



A GREAT FINISH. FBRS415 flush ceiling installation.





1 Cut hole in ceiling. Remove box from sled and fit mounting bracket into hole. Position bracket between joists, with bracket feet resting on the ceiling.



Tighten the hex bar with a wrench to secure bracket between joists.




Reattach box, and center it in hole. Attach bracket with screws supplied. Install fan/fixture per manufacturer's instructions.

#### FBRS420R

for Existing Construction

- Mounts between joists or rafters 16" to 24" o.c
- 20.0 cubic inch
- UL Rated: 35 lb. fans, 50 lb. fixtures
- CSA: Fans/fixtures up to 50 lbs.

### For Wood I-Beams in Existing Construction



Wood I-beams

#### FBRS407R

for Wood I-Beams in Existing Construction

- Box installs flush with ceiling drywall
- For 1/2" and 5/8" thick ceilings
- No parts to lose ships with captive box adjustment screws, fan bracket installation screws and an installed NM cable connector
- 8.0 cubic inch box
- For existing construction on wood I-beams or rafters set 16 to 24 inches on-center
- Listed to new UL standards
- UL rating 35 lb. fan • 50 lb. fixture

Designed just for mounting a fan or fixture on a suspended ceiling grid, Arlington's FBRS420SC fan/fixture box kit saves money! And 30 minutes of installation time.

The box/bracket assembly ships with the box mounted securely on-center, ready to install on a 24" grid. For a centered installation, there's no need to adjust the box or bracket, but you can position the box where you want it.

There are no parts to lose! FBRS420SC ships fully assembled. Installation and adjustment screws ship parked in place. There's an installed NM cable connector too.

- Fully adjustable mounting bracket
- 2" deep, 20.0 cubic inch box
- Meets new UL standards
- UL Rating: 70 lb fan or fixture
   CSA: Acceptable for fan support
- Usable for Environmental Air Handling spaces





Cut a 4-1/16" diameter hole in a 24" ceiling tile.




Place box over hole. Place ends of support bar over the ceiling grid (tees).



Use the "S" hooks provided to attach chain to turnbuckle, and chain to the overhead support. Use turnbuckle to apply tension to the chain, so it supports the weight of fan.




4 Remove captive screws (shown above). Use them to install the fan or fixture per manufacturer's specifications, NEC and all local electrical codes.



Item# UPC/DCI/NAED Box Description Unit/Std

Item #	UPC/DCI/NAED MFG #01 899	Вох	Description	Unit/Std Pkg
FBRS420SC	75300	2" deep 20.0 cu. in.	Fan/Fixture box kit for suspended ceilings	1/5

## UL Listed for fixtures up to 50 lbs.





Cut a 4-1/16" diameter hole in a 24" ceiling tile.

4 Cable pulled through cable

connector (not supplied).



2 Place box over hole.



3 Snap ends of support bar over the ceiling grid (tees).



Use FS420SCL to install fixtures, security cameras, etc. Not fan rated.

Item #	UPC/DCI/NAED MFG #01 899	Вох	Description	Unit/Std Pkg
FS420SCL	12526	2" deep 20.0 cu. in.	Box for suspended ceilings, for fixtures up to 50 lbs.	1/10

One-piece, rated unit includes box, bracket and drop wire

Arlington's new all-metal box, just for fixtures, is a one-piece assembly that ships ready to install on a 24" suspended ceiling grid – No assembly required.

It's tested and rated to support exit lights, security cameras – and other light fixtures up to 50 lbs.

No more guesswork.
Installers who previously
attached a metal box to a
bracket in the field, then
added a chain or wire for
support, now have an
assembly that is fully tested
to hold up to 50 lbs!

If the box is not perfectly positioned, loosen the appropriate screws, slide the box along the bracket and retighten the screws.

- Easy, secure mounting to ceiling grid
- Costs less than fieldassembled components (box, bracket, wire)
- Saves installation time
- Usable for Environmental Air Handling spaces



For FBRS420SC and FS420SCL

OPTION: If required by local code, use sheet metal screws (not supplied) to hold bracket ends on ceiling grid.



#### FB405

for 1/2" and 5/8" drywall

#### FB407

for 5/8" drywall

#### FB412

for 1/2" or 5/8" drywall with hat channel or furring strips, or double drywall

FB405, FB407, and FB412 offer the flexible, economical solution to 1/2" and 5/8" drywall ceiling, with or without hat channel or furring strips. FB405 and FB407 are perfect for double joists or wood I-beams.

- Fast, easy installation
- Secure attachment to joist or rafter
- No parts to lose
- 2-hour fire rating
- UL Rated: 70 lb. fans, fixtures up to 200 lbs.
- CSA: Fans/fixtures up to 50 lbs.



### **Box Installation**



The FB412 fan/fixture box is perfect for 1/2" or 5/8" drywall with 3/4" furring strips or hat channel with a single layer of drywall...




2 ...or double drywall (shown as cutaway).



Item #	UPC/DCI/NAED	Cubic	Drywall	Unit/Std
	MFG #01 899	Inches	Thickness	Pkg
FB405	72185	6.0	1/2" or 5/8"	25
FB407	72177	8.0	5/8"	25
FB412	72189	14.5	1/2" or 5/8" *	25

\* w/ furring strips or hat channel with a single layer of drywall or with a double layer of drywall





**NEW!** Flanged design forms a protective barrier against air infiltration.

FB426F

Item #	UPC/DCI/NAED MFG #01 899	Cubic Inches	Drywall Thickness	Unit/Sto
FB415	72167	10.3	1/2" or 5/8"	25
FB426	72179	16.0	1/2" or 5/8"	25
FB426F	12521	16.0	1/2" or 5/8"	25
FB423	72190	19.5	1/2" or 5/8" *	25

\* w/ furring strips or hat channel with a single layer of drywall or with a double layer of drywall



1 Convenient. Gripping tangs hold box in place temporarily, until the center screw is tightened.



Push NM sheathed cable through connector.



Remove (2) long parked screws. Use them to install bracket.



The fan/fixture bracket installs directly onto the joist through the oval slots in the box.



5 Cable pulled through installed NM cable connector.

All of Arlington's Fan/Fixture boxes ship with an installed NM cable connector and mud cover – as well as captive installation screws for the box and bracket.

No parts to lose or misplace...ready to use!

#### FB415

for 1/2" and 5/8" drywall

#### FB426

for 1/2" and 5/8" drywall

#### FB423

for 1/2" or 5/8" drywall with hat channel or furring strips with a single layer of drywall, or double drywall

FB415 and FB426 come with the screws you need to install the box and bracket, held captive until you're ready to use them.

Press Hold...Speed, Convenience, Safety

These boxes have gripping tangs that press-hold the box to the joist while you reach for your screwdriver. Tightening the center screw affixes the box onto the joist for a supersecure installation.

- 2-hour fire rating
- UL Rated: 70 lb. fans, fixtures up to 200 lbs.
- CSA: Fans/fixtures up to 50 lbs.



11

#### FB444

**Our largest capacity** L-shaped box


#### FB442 FB443

**Lowest cost L-shaped boxes** 

FB444 is the largest capacity box we make! Its 25.6 cubic inch capacity provides plenty of room for wires - easy access too!

The slightly smaller FB443 and FB442 offer the same great features and benefits at a lower cost.

- Boxes mount to single or double joists or rafters with a shipped-in-place center
- Locator posts assure correct positioning of bracket
- UL Rated: 70 lb. fans, fixtures up to 200 lbs.
- **CSA:** Fans/fixtures up to 50 lbs.
- 2-hour fire rating





#### **FB442 Installation**



1 Secure! Side mount the box to the joist using the shipped-in-place



2 Pull wires. (Drywall installation omitted) After ceiling is installed. remove captive installation screws - use them to install bracket.



3 Done! Install fan or fixture per manufacturer's instructions.

#### FB444 Installation



Fast and easy installation on single or double joists!



Easy. Bracket installation on FB444. (Drywall installation not shown)





2 Accurate! Locator posts on these L-shaped boxes assure proper positioning of the installation bracket.



Easy access. FB444 OPTION: To restuff wires, open bottom of the box – before drywall installation.

### Nail On Attachment to Single or Double Joists







Fast. Simply nail the box to the joist. Indicator lines on FB417S assure proper positioning on the joist fo the ceiling thickness.

		A condition
•		FB417S
s or		'S and FB417SLP side mount to single or e joists for a super-secure installation.
	Unit/Std	Most of Arlingto

UPC/DCI/NAED Ceiling MFG #01 899 Thickness FB417S 72177 up to 1-1/2" 25 FB417SLP\* 72199 20.0 1/2" or 5/8"

Most of Arlington's Fan/Fixture boxes ship with an installed NM cable connector and mud cover As well as captive installation screws for the box and bracket.

No parts to lose or misplace... ready to use!

#### FB417S

for ceilings up to 1-1/2" thick, including single-sheeted drywall mounted to furring strips or hat channel or double drywall

#### FB417SLP Low profile for

1/2" or 5/8" ceilings

FB417S saves time! Nail on installation, and indicator marks for 1/2", 5/8", and 3/4" ceiling thicknesses make it the logical choice for speedy attachment to single or double joists.

For added convenience, use the low profile FB417SLP for 1/2" or 5/8" ceilings. Also works for manufactured I-beams.

Both ship ready to use, with the nail in place and captive bracket installation screws.

- No loose parts totally self-contained
- Combination hex/Phillips head screws for easy installation with power screwdrivers
- Nail on installation
- 20.0 cubic inch
- 2-hour fire rating
- UL Rated: Fans/ fixtures up to 70 lbs.
- CSA: Fans/fixtures up to 50 lbs.

13



<sup>\*</sup> Also works on manufactured I-beams

#### MB8

**6.1 Cubic inches** 

- Ceiling medallion and electrical box combined
- Supports flood lights, smoke detectors, fans, light fixtures – any fixture needing a safe, strong installation.
- UV rated plastic
- For interior or exterior use
- Mounts directly to soffit or ceiling joist without the need to cut ceiling drywall
- Paintable
- UL Rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

Canadian orders ship with grounding lug required by CSA for use with fixtures.



#### MB8 includes...

Two #10 x 3" wood screws, one #8 x 1-1/2" wood screw, two KOs, and one NM94 non-metallic cable connector.

Item #	UPC/DCI/NAED	Cubic	Use and	Unit/Std
	MFG #01 899	Inches	Box Depth	Pkg
MB8	42330	6.1	Flat Mount	1/10

#### **MB8** Installation



1 Locate the ceiling joist using a stud finder or similar device. Drill a hole approximately 1/2" in diameter, in the ceiling next to the joist. Remove desired knockout. Insert the cable connector into the opening. Pull the NM cable through the connector.

Tapped #8-32

(for fixtures)

Tapped #10-32 for fans

(screws included)



2 Using the #8 x 1-1/2" wood screws 3 Install the fixture or fan mounting provided, mount the MB8 to the joist (through the ceiling).



bar (provided with the fixture or fan) directly to the joist with the (2) #10 x 3" wood screws and lock washers provided. Wire the fixture or fan following the instructions included with the product.

Three screws ship captive

and attach box securely to

Tapped #10-32

(screws included)

FBS1423

Patent Pending

## Steel Box – Side Mounts to Joist NEW!

#### FBS1423

23.0 Cubic inches

Designed for new construction or retrofit, this deep steel box side mounts to a joist for a super secure, fan-rated installation.

- UL Rated for fans/fixtures up to 70 lbs.
- CSA: Fans/fixtures up to 50 lbs.



Installed NM cable connector 3/4" KO on side

Place box at proper depth; attach to joist with three captive screws in the box.

Item #	UPC/DCI/NAED	Cubic	Side Mount	Unit/Std
	MFG #01 899	Inches	Box Depth	Pkg
FBS1423	76190	23.0	2.375"	10

Tapped #8-32 (for fixtures)

# Fan/Fixture Box Rating and # of Single Conductors

Catalog Number	Category	Cubic Inches (Lbs.)	UL Fan Load Rating (Lbs.)	CSA Fan Load Rating (Lbs.)	UL Fixture Static Rating (Lbs.)	CSA Fixture Static Rating	# Of Single #14 or	Conductors #12 or	#10
FB405	PLASTIC	6.0	70	50	200	50	3	_	_
FB4050	PLASTIC	6.0	70	50	200	50	3	_	_
FB407	PLASTIC	8.0	70	50	200	50	4	3	3
FB4070	PLASTIC	8.0	70	50	200	50	4	3	3
FB412	PLASTIC	14.4	70	50	200	50	7	6	5
FB415	PLASTIC	10.3	70	50	200	50	5	4	4
FB4150	PLASTIC	10.3	70	50	200	50	5	4	4
FB417S	PLASTIC & STEEL	20.0	70	50	70	50	10	8	8
FB417SLP	PLASTIC & STEEL	20.0	70	50	70	50	10	8	8
FB423	PLASTIC	19.5	70	50	200	50	9	8	7
FB426	PLASTIC	16.0	70	50	200	50	8	7	6
FB426F	PLASTIC	16.0	70	50	200	50	8	7	6
FB442	PLASTIC	13.4	70	50	200	50	6	4	4
FB443	PLASTIC	17.96	70	50	200	50	8	7	7
FB444	PLASTIC	25.6	70	50	200	50	13	11	10
FB450	PLASTIC	14.5	70	50	200	50	7	6	5
FB900	PLASTIC	14.5	70	50	200	50	7	6	5
FBRS407R	STEEL	8.0	35	50	50	50	4	3	3
FBRS415	STEEL	15.6	70 @ 24" o.c. 110 @ 16" o.c.	50	70 @ 24" o.c. 110 @ 16" o.c.	50	7	6	6
FBRS420R	STEEL	20.0	35	50	50	50	10	8	8
FBRS420SC	STEEL	20.0	35	50	50	50	10	8	8
FBS1423	STEEL	23.0	70	50	70	50	11	10	9
FBS405	STEEL	6.0	70	50	200	50	3	-	-
FBS405T	STEEL	6.0	70	50	200	50	3	-	-
FBS407	STEEL	8.0	70	50	200	50	4	3	3
FBS407T	STEEL	8.0	70	50	200	50	4	3	3
FBS415	STEEL	14.6	70	50	200	50	7	6	6
FBS415S	STEEL	14.6	70	50	70	50	7	6	6
FBS420	STEEL	20.0	70	50	200	50	10	8	8
FBS420S	STEEL	20.0	70	50	70	50	10	8	8
FBX900	PLASTIC & STEEL	14.5	70	50	70	50	7	6	5
FS420SCL	STEEL	20.0	_	_	25	25	10	8	8
MB8	PLASTIC	6.1	70	50	200	50	3	_	_

Most of of Arlington's Fan/Fixture boxes ship with an installed NM cable connector and mud cover – As well as captive installation screws for the box and bracket.

No parts to lose or misplace...ready to use!



15 14

# SAVE MONEY!

**FAN/FIXTURE BOX just for SUSPENDED CEILINGS** 



Save 30 minutes of assembly time with Arlington's new fan/fixture box. It ships with the box and bracket assembly mounted on center, ready to install on a 24" suspended ceiling grid.

- No parts to lose
- Installation and adjustment screws ship captive
- 2" deep, 20.0 cu. inch box





# FLUSH WITH CEILING

**FAN/FIXTURE BOX with ADJUSTABLE BRACKET** 



Arlington's heavy-duty, plated steel fan/fixture box has an adjustable bracket that fits 16" to 24" o.c.

#### Flush ceiling installations!

FBRS415 is designed for ceilings up to 1-1/4" thick. For 1/2" ceilings, use the pre-bent positioning tab.



- 15.6 cu. inch box
- Ships with captive screws, mud cover, installed NM cable connector


FS420SCL



# FIXTURE BOX TESTED WEIGHT RATING LISTED AS 1-PIECE UNIT

pg 9

for SUSPENDED CEILINGS



Arlington's new all-metal, one-piece fixture box ships ready to install on a 24" suspended ceiling grid. There's no assembly required!

It's tested and rated to support exit lights, security cameras and other light fixtures up to 50 lbs.

**No more guesswork.** Installers who attached a metal box to a bracket in the field, then added a chain or wire for support, now have an assembly that's *fully tested* to hold *up to 50 lbs!* 

FS420SCL is UL/CSA Listed as a complete unit: box, bracket, drop wire.

- Box can be positioned anywhere along bracket
- Costs less than field-assembled components (box, bracket, wire)
- Usable for Environmental Air Handling spaces



1 Stauffer Industrial Park Scranton, PA 18517 800/233.4717 Fax 570/562.0646

www.aifittings.com

**Arlington** 

©2008 Arlington Industries, Inc.

Arlington's fan/fixture boxes are patented (or other patents pending).