





GE
Lighting

86256 - FLE13HT2/2/827

GE Spiral® T2



GENERAL CHARACTERISTICS

| | |
|---------------------------------|--------------------------------------|
| Lamp Type | Compact Fluorescent - Self-Ballasted |
| Bulb | T2 |
| Base | Medium Screw (E26) |
| Bulb Finish | Soft white |
| Equivalent Wattage | 60.0 W |
| Rated Life | 12000.0 hrs |
| Starting Temperature (MIN) | 5.0 °C |
| Total Harmonic Distortion (THD) | 120.0 % |
| LEED-EB MR Credit | 600 picograms Hg per mean lumen hour |
| Primary Application | Standard |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------|----------|
| Initial Lumens | 870.0 |
| Mean Lumens | 695.0 |
| Nominal Initial Lumens per Watt | 66 |
| Color Temperature | 2700.0 K |
| Color Rendering Index (CRI) | 82.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|----------|
| Wattage | 13.0 |
| Input Voltage | 120.0 V |
| Input Current | 0.1900 A |
| Power Factor | 0.5 |

DIMENSIONS

| | |
|------------------------------|--------------------|
| Maximum Overall Length (MOL) | 3.9000 in(99.1 mm) |
| Nominal Length | 3.900 in(99.1 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 86256 |
| Description | FLE13HT2/2/827 |
| Standard Package | Case |
| Standard Package GTIN | 10043168862568 |
| Standard Package Quantity | 10 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 10 |
| UPC | 043168862561 |

NOTES



- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.



GE
Lighting

86256 - FLE13HT2/2/827

GE Spiral® T2



GENERAL CHARACTERISTICS

| | |
|---------------------------------|--------------------------------------|
| Lamp Type | Compact Fluorescent - Self-Ballasted |
| Bulb | T2 |
| Base | Medium Screw (E26) |
| Bulb Finish | Soft white |
| Equivalent Wattage | 60.0 W |
| Rated Life | 12000.0 hrs |
| Starting Temperature (MIN) | 5.0 °C |
| Total Harmonic Distortion (THD) | 120.0 % |
| LEED-EB MR Credit | 600 picograms Hg per mean lumen hour |
| Primary Application | Standard |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------|----------|
| Initial Lumens | 870.0 |
| Mean Lumens | 695.0 |
| Nominal Initial Lumens per Watt | 66 |
| Color Temperature | 2700.0 K |
| Color Rendering Index (CRI) | 82.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|----------|
| Wattage | 13.0 |
| Input Voltage | 120.0 V |
| Input Current | 0.1900 A |
| Power Factor | 0.5 |

DIMENSIONS

| | |
|------------------------------|--------------------|
| Maximum Overall Length (MOL) | 3.9000 in(99.1 mm) |
| Nominal Length | 3.900 in(99.1 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 86256 |
| Description | FLE13HT2/2/827 |
| Standard Package | Case |
| Standard Package GTIN | 10043168862568 |
| Standard Package Quantity | 10 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 10 |
| UPC | 043168862561 |

NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.