



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CT8NT120L 8" Natural 120 LB

Minnesota Mining (3M)

| | |
|------------------|---|
| Catalog Number | CT8NT120L |
| Manufacturer | Minnesota Mining (3M) |
| Description | 3M™ Standard Nylon Cable Ties Are Made With High-Quality Nylon 6/6 and Designed to Secure Wire Bundles and Harness Components Quickly, Without Slipping. The Curved Tip Allows For Faster Threading and Installation, and They Feature A Self-Locking Head. |
| Weight per unit | 2.0 (lbs/each) |
| Product Category | Cable Ties & Wraps |

Descriptions

| | |
|------------------------|--|
| Description | 8" NATURAL 120 LB |
| extra long description | 3M 7000133465 3M™ Standard Nylon Ca |
| Features | 3M™ Standard Nylon Cable Ties are available in several tensile strengths ranging from 18 lb. to 175 lb. and multiple lengths ranging from 4 inches to 48 inches to cover your needs. They are offered in natural and red for indoor use and UV weather-resistant black for indoor and outdoor use. UL Listed 62275 Type 21 or 21S and Plenum Rated AH-2 for use in air handling spaces. Made in the USA. |
| Long Description | 3M™ Standard Nylon Cable Ties are made with high-quality nylon 6/6 and designed to secure wire bundles and harness components quickly, without slipping. The curved tip allows for faster threading and installation, and they feature a self-locking head. |
| Product Type | 3M™ Standard Nylon Cable Ties |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | 3M |
| GTIN | 00051128593110 |
| Manufacturers Part Number | 7000133465 |
| UPC | 051128593110 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
|----------------------|----------------------------|

Packaging

| | |
|-----------------|-----|
| Carton | 500 |
| Weight Per each | 2 |