



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GDB2A 2A 250V Fa Low-Break IEC Glass Fuse

*Bussmann Fuses*

|                  |   |
|------------------|---|
| Catalog Number   | GDB2A   |
| Manufacturer     | Bussmann Fuses  |
| Description      | Fuse, Fast Acting Fuse Speed, Ferrule End X Ferrule End Connection, 2 A, 250 V Ac, Glass (Tube);Brass (End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length, 0.004 LB |
| Weight per unit  | 0.0040 (lbs/each)   |
| Product Category | Small Dimension Fuses   |

### Features

|                 |                           |
|-----------------|---------------------------|
| amp rating      | 2                         |
| amperage rating | 2 A                       |
| connection      | Ferrule End X Ferrule End |
| dimensions      | X X 0.7874 IN             |
| low break glass | Fast Acting               |

### Dimensions and Weight

|      |                                    |
|------|------------------------------------|
| Size | 5.20 mm Diameter X 20.00 mm Height |
|------|------------------------------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 2A 250V FA LOW-BREAK IEC GLASS FUSE   |
| extra long description | EFSE GDB-2A BUSS SMALL DIMENSION FU   |
| Features               | Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse |
| Special Features       | Low Breaking Capacity, Interrupt Rating 35 Amp at 250 V, Material Glass Tube, Nickel Plated Brass Endcap  |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00051712431798 |
| UPC   | 051712431798   |

### Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type                 | Fast-Acting Fuse          |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 5     |
| Weight Per each | 0.004 |

## Uses, Certifications, and Standards

|                  |   |
|------------------|---|
| Frequency Rating | 50                                      |
| standard         | VDE,CCC Marked,CE Marked,RoHS Compliant |