



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GDB5A 5A 250V Fa Low-Break IEC Glass Fuse

*Bussmann Fuses*

Catalog Number	GDB5A
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, Ferrule End X Ferrule End Connection, 5 A, 250 V Ac, Glass (Tube);Brass (End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length
Weight per unit	0.0050 (lbs/each)
Product Category	Small Dimension Fuses

### Features

amperage rating	5 A
connection	Ferrule End X Ferrule End
dimensions	X X 0.7874 IN

### Dimensions and Weight

Size	5.20 mm Diameter X 20.00 mm Height
------	------------------------------------

### Descriptions

Description	5A 250V FA LOW-BREAK IEC GLASS FUSE
extra long description	BUSS GDB-5A BUSS SMALL DIMENSION FU
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse
Special Features	Low Breaking Capacity, Interrupt Rating 50 Amp at 250 V, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712431835
UPC	051712431835

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse

### Packaging

Carton	1
Package	5
Weight Per each	0.005



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Frequency Rating	50
standard	VDE,RoHS Compliant,CE Marked,CCC Marked