

Axial Lead and Cartridge Fuses

Midget

250 Vac / 125 Vdc Slow-Blo Type Fuse FLM Series

PS UL SP QPL

ELECTRICAL CHARACTERISTICS:

| % of Ampere Rating | Ampere Rating | Opening Time |
|--------------------|---------------|----------------------------|
| 135% | 1/10-30 | 1 hour, Maximum |
| | 32/10-30 | 12 seconds, Minimum |
| 200% | 0-3 | 5 seconds, Minimum |


VOLTAGE RATINGS: 250 Vac
125 Vdc self-certified @ 10 kA

INTERRUPTING RATING: 10,000 amperes at 250 Vac


AGENCY APPROVALS: UL Listed (File:E10480)
CSA Certified (029862_0_000)

ORDERING INFORMATION:

| Cartridge Catalog Number | Ampere Rating | AC Voltage Rating | Nominal Resistance Cold Ohms |
|------------------------------------|---------------|-------------------|------------------------------|
| FLM 1/10 | .100 | 250 | 188.0 |
| FLM 15/100 | .150 | 250 | 87.0 |
| FLM 2/10 | .200 | 250 | 35.109 |
| FLM 1/4 | .250 | 250 | 16.82 |
| FLM 3/10 | .300 | 250 | 6.739 |
| FLM 4/10 | .400 | 250 | 5.413 |
| FLM 1/2 | .500 | 250 | 3.79 |
| FLM 6/10 | .600 | 250 | 2.05 |
| FLM 8/10 | .800 | 250 | 1.024 |
| FLM 1 | 1 | 250 | 1.024 |
| FLM 1 ¹ / ₈ | 1.125 | 250 | .6231 |
| FLM 1 ¹ / ₄ | 1.25 | 250 | .6231 |
| FLM 1 ⁴ / ₁₀ | 1.4 | 250 | .395 |
| FLM 1 ¹ / ₂ | 1.5 | 250 | .339 |
| FLM 1 ⁶ / ₁₀ | 1.6 | 250 | .286 |
| FLM 1 ⁸ / ₁₀ | 1.8 | 250 | .253 |
| FLM 2 | 2 | 250 | .2191 |
| FLM 2 ¹ / ₄ | 2.25 | 250 | .184 |
| FLM 2 ¹ / ₂ | 2.5 | 250 | .162 |
| FLM 2 ⁹ / ₁₀ | 2.8 | 250 | .125 |
| FLM 3 | 3 | 250 | .102 |
| FLM 3 ³ / ₁₀ | 3.2 | 250 | .0904 |
| FLM 3 ¹ / ₂ | 3.5 | 250 | .0735 |
| FLM 4 | 4 | 250 | .0400 |
| FLM 4 ¹ / ₂ | 4.5 | 250 | .0561 |
| FLM 5 | 5 | 250 | .0413 |
| FLM 5 ⁶ / ₁₀ | 5.6 | 250 | .0326 |
| FLM 6 | 6 | 250 | .0280 |
| FLM 6 ¹ / ₄ | 6.25 | 250 | .0277 |
| FLM 7 | 7 | 250 | .02133 |
| FLM 8 | 8 | 250 | .01247 |
| FLM 9 | 9 | 250 | .01066 |
| FLM 10 | 10 | 250 | .00903 |
| FLM 12 | 12 | 250 | .00698 |
| FLM 15 | 15 | 250 | .00530 |
| FLM 20 | 20 | 250 | .00385 |
| FLM 25 | 25 | 250 | .00275 |
| FLM 30 | 30 | 250 | .00226 |



Average Time Current Curves



Axial Lead and Cartridge Fuses

Midget

250 Vac / 125 Vdc Slow-Blo Type Fuse FLM Series

PS UL SP QPL

ELECTRICAL CHARACTERISTICS:

| % of Ampere Rating | Ampere Rating | Opening Time |
|--------------------|---------------|----------------------------|
| 135% | 1/10-30 | 1 hour, Maximum |
| | 32/10-30 | 12 seconds, Minimum |
| 200% | 0-3 | 5 seconds, Minimum |


VOLTAGE RATINGS: 250 Vac
125 Vdc self-certified @ 10 kA

INTERRUPTING RATING: 10,000 amperes at 250 Vac

AGENCY APPROVALS: UL Listed (File:E10480)
CSA Certified (029862_0_000)

ORDERING INFORMATION:

| Cartridge Catalog Number | Ampere Rating | AC Voltage Rating | Nominal Resistance Cold Ohms |
|--------------------------|---------------|-------------------|------------------------------|
| FLM 1/10 | .100 | 250 | 188.0 |
| FLM 15/100 | .150 | 250 | 87.0 |
| FLM 2/10 | .200 | 250 | 35.109 |
| FLM 1/4 | .250 | 250 | 16.82 |
| FLM 3/10 | .300 | 250 | 6.739 |
| FLM 4/10 | .400 | 250 | 5.413 |
| FLM 1/2 | .500 | 250 | 3.79 |
| FLM 6/10 | .600 | 250 | 2.05 |
| FLM 8/10 | .800 | 250 | 1.024 |
| FLM 1 | 1 | 250 | 1.024 |
| FLM 1 1/8 | 1.125 | 250 | .6231 |
| FLM 1 1/4 | 1.25 | 250 | .6231 |
| FLM 1 4/10 | 1.4 | 250 | .395 |
| FLM 1 1/2 | 1.5 | 250 | .339 |
| FLM 1 6/10 | 1.6 | 250 | .286 |
| FLM 1 8/10 | 1.8 | 250 | .253 |
| FLM 2 | 2 | 250 | .2191 |
| FLM 2 1/4 | 2.25 | 250 | .184 |
| FLM 2 1/2 | 2.5 | 250 | .162 |
| FLM 2 9/10 | 2.8 | 250 | .125 |
| FLM 3 | 3 | 250 | .102 |
| FLM 3 1/10 | 3.2 | 250 | .0904 |
| FLM 3 1/2 | 3.5 | 250 | .0735 |
| FLM 4 | 4 | 250 | .0400 |
| FLM 4 1/2 | 4.5 | 250 | .0561 |
| FLM 5 | 5 | 250 | .0413 |
| FLM 5 9/10 | 5.6 | 250 | .0326 |
| FLM 6 | 6 | 250 | .0280 |
| FLM 6 1/4 | 6.25 | 250 | .0277 |
| FLM 7 | 7 | 250 | .02133 |
| FLM 8 | 8 | 250 | .01247 |
| FLM 9 | 9 | 250 | .01066 |
| FLM 10 | 10 | 250 | .00903 |
| FLM 12 | 12 | 250 | .00698 |
| FLM 15 | 15 | 250 | .00530 |
| FLM 20 | 20 | 250 | .00385 |
| FLM 25 | 25 | 250 | .00275 |
| FLM 30 | 30 | 250 | .00226 |



Average Time Current Curves

