



FNM30 30A 32V TD Midget Fuse

Bussmann Fuses

Catalog Number	FNM30
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNM Fuse, Time-Delay Midget Fuse, 30 A, Dual, Non-Indicating, Ferrule End X Ferrule End, 10 KAIC At 250 Vac, Nickel-Plated Bronze Endcap, Standard, 250 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

dimensions	0.3900 IN X 0.3900 IN X 1.4400 IN
Material	Nickel-plated bronze endcap
media	Yes

Descriptions

Description	30A 32V TD MIDGET FUSE
extra long description	EFSE FNM-30 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNM fuse, Time-delay Midget fuse, 30 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V
Product Type	Buss Midget Fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712523004
Manufacturers Part Number	FNM-30
UPC	051712523004

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application standard	Ind Facilities & Factories - Facility: Safety and Security Systems CE Marked, RoHS Compliant
----------------------	---