

Straight Blade Devices  
 20A, 125V, 2 Pole, 3 Wire Grounding  
 Insulgrip Plug

# HUBBELL

## Features

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

## Ordering Information

| Description           | Cord Diameter         | UPC          | Catalog Number |
|-----------------------|-----------------------|--------------|----------------|
| Black and white nylon | .230"-.720"(5.8-18.3) | 783585173955 | HBL5366C       |



## Listings

UL Listed to UL498 File E1706  
 CSA Certified to C22.2 No. 42 File 280  
 Fed. Spec. W-C596G  
 NEMA® WD-6 Compliant

## Specifications

|                    |                              |
|--------------------|------------------------------|
| Housing/Cord Clamp | Nylon                        |
| Blade Holder       | Nylon                        |
| Terminal Retainer  | Clear Polycarbonate          |
| Blades             | .060 in. (1.5) Brass         |
| Terminal Screws    | #8-32 Brass , multiple drive |
| Terminal Clamp     | Nickel plated steel          |
| Assembly Screws    | Nickel plated steel          |

## Performance

### Electrical



|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

### Mechanical

|                         |  |
|-------------------------|--|
| Cord Accomodation       | .230"-.720"(5.8-18.3)                                  |
| Terminal Accommodation  | #18-10 AWG. Standed copper wire only                   |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

### Environmental

|                        |   |
|------------------------|---|
| Flammability           | UL 94 HB or better                                  |
| IP Suitability         | IP20  |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |



## Accessories

|                   |         |
|-------------------|---------|
| Weatherproof Boot | HBL6017 |
|-------------------|---------|

## Resources

Customer Use Drawing  
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Straight Blade Devices  
 20A, 125V, 2 Pole, 3 Wire Grounding  
 Insulgrip Plug



**Features**

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

**Ordering Information**

| Description           | Cord Diameter         | UPC          | Catalog Number |
|-----------------------|-----------------------|--------------|----------------|
| Black and white nylon | .230"-.720"(5.8-18.3) | 783585173955 | HBL5366C       |



**Listings**

UL Listed to UL498 File E1706  
 CSA Certified to C22.2 No. 42 File 280  
 Fed. Spec. W-C596G  
 NEMA® WD-6 Compliant

**Specifications**

|                    |                              |
|--------------------|------------------------------|
| Housing/Cord Clamp | Nylon                        |
| Blade Holder       | Nylon                        |
| Terminal Retainer  | Clear Polycarbonate          |
| Blades             | .060 in. (1.5) Brass         |
| Terminal Screws    | #8-32 Brass , multiple drive |
| Terminal Clamp     | Nickel plated steel          |
| Assembly Screws    | Nickel plated steel          |

**Performance**

**Electrical**



Current Interrupting Certified for current interrupting at full rated current  
 Dielectric Voltage Withstands 2,000V minimum

**Mechanical**

Cord Accomodation .230"-.720"(5.8-18.3)  
 Terminal Accommodation #18-10 AWG. Standed copper wire only  
 Terminal Identification Terminals identified in accordance with UL 498 and CSA

**Environmental**

Flammability UL 94 HB or better  
 IP Suitability IP20  
 Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



**Accessories**

|                   |         |
|-------------------|---------|
| Weatherproof Boot | HBL6017 |
|-------------------|---------|

**Resources**

Customer Use Drawing  
 eCatalog