



## FNQR7 Class CC TD Fuse

Bussmann Fuses

Catalog Number	FNQR7
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class CC Fuse, FNQ, Time-Delay, Dual-Element Current Limiting Fuse, 7 A, Rejection Style Fuse, Interrupting Rating Of 200KA At 600vac
Weight per unit	0.0150 (lbs/each)
Product Category	Dual Element

### Features

amperage rating	7
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
Fuse Class	Class CC
interrupt rating	200 KAIC
Material	Melamine Tube; Nickel-plated brass endcap
media	Yes
Response Time	12 Seconds Minimum at 200%
Voltage Rating	600 V

### Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

### Descriptions

Description	CLASS CC TD FUSE
extra long description	BUSS FNQ-R-7 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 7 A, rejection style fuse, interrupting rating of 200kA at 600Vac
Product Type	Class CC Time Delay
Special Features	Rejection Style



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712558259
Manufacturers Part Number	FNQ-R-7
UPC	051712558259

## Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

## Packaging

Carton	10
Weight Per each	0.015

## Uses, Certifications, and Standards

Application standard	Ind Facilities & Factories - Facility: Safety and Security Systems RoHS Compliant,CE Marked
----------------------	--