



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9
78620-0000, TX Dripping Springs
Phone: 737-317-5073
Fax: 737-317-5074



GASK684R 1-1/2" Rubber Gasket *Crouse-Hinds*

Catalog Number	GASK684R
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet LBD Replacement Gasket, Neoprene, 1-1/2" or 2", Used With LBD5500 or LBD6600 Moguls
Weight per unit	0.1100 (lbs/each)
Product Category	Bodies & Covers

Features

connection	Water Jet Cut
dimensions	11.7500 IN X 0.0100 IN X 5.0000 IN
Material	Neoprene

Material, Color, and Finish

Color	Black
Finish	Black

Descriptions

Description	1-1/2" RUBBER GASKET
extra long description	CRS-H GASK684R 1 1/2 - 2 NEO LBD RE
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet LBD replacement gasket, Neoprene, 1-1/2" or 2", Used with LBD5500 or LBD6600 moguls
Product Type	1 1/2 - 2 Neo LBD Replacement Gask

Manufacturer Information

Brand	Eaton
GTIN	00782274436500
Manufacturers Part Number	GASK684R
UPC	782274436500

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Replacement gasket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9
78620-0000, TX Dripping Springs
Phone: 737-317-5073
Fax: 737-317-5074

Packaging

Carton	1
Package	25
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2