



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB2100 Type GHB Breakr 2P 100A 277/480VAC Max 125/250VDC *Eaton Corp*

Catalog Number	GHB2100
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 100 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ
Weight per unit	1.2 (lbs/each)
Product Category	2 Pole

Features

Current Rating	100 A
dimensions	2.6300 IN X 2.0000 IN X 4.0000 IN
frame	G
Poles	Two-pole
Voltage Rating	480Y/277 Vac, 125/250 Vdc

Descriptions

Description	TYPE GHB BREAKR 2P 100A 277/480VAC MAX 125/250VDC
extra long description	ETN GHB2100 GHB CCB 2P100A 277/480V
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 100 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz
Product Type	GHB CCB 2P100A 277/480VAC Max 125/250VDC

Manufacturer Information

Brand	Eaton
GTIN	00786679911242
Manufacturers Part Number	GHB2100
UPC	786679911242

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.15

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL Listed,Federal Specifications Classification W-C375B