



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL8300I Dup RCPT, HG, 20A 125V, 5-20R, Iv** *Hubbell Wiring Devices*

|                  |  |
|------------------|--|
| Catalog Number   | HBL8300I   |
| Manufacturer     | Hubbell Wiring Devices   |
| Description      | Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack. |
| Weight per unit  | 0.2500 (lbs/each)  |
| Product Category | Gen Purpose Recept & Surge Pro   |

### **Features**

|                     |                                     |
|---------------------|-------------------------------------|
| amperage rating     | 20                                  |
| connection          | Back and Side Wired Screw Terminals |
| Current Rating      | 20                                  |
| Dielectric Strength | Withstands 2,000V minimum           |
| Number of Wires     | 3-Wire                              |
| pallet quantity     | 5500                                |
| Phase               | 1                                   |
| Poles               | 2-Pole                              |
| Voltage Rating      | 125 V                               |
| Wattage             | 2500                                |
| Wire Size           | #12 to #10                          |

### **Dimensions and Weight**

|      |                             |
|------|-----------------------------|
| Size | 3.28 in x 1.65 in x 1.19 in |
|------|-----------------------------|

### **Descriptions**

|                        |  |
|------------------------|--|
| Description            | DUP RCPT, HG, 20A 125V, 5-20R, IV  |
| extra long description | HWDK HBL8300I DUP RCPT, HG, 20A 125  |
| Features               | HBL® Extra Heavy Duty Max Hospital Grade Devices - UL requirements for Hospital Grade devices is more stringent than those for standard devices. Hubbell receptacles are designed to meet and exceed the standards with Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature; Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas; Impact resistant deep face design prevents breakage. Because of these |
| Long Description       | Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.   |
| Product Type           | Dup RCPT, HG, 20A 125V, 5-20R, Iv  |
| Special Features       | Self Grounding   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585435725        |
| Manufacturers Part Number | HBL8300I              |
| series                    | Hospital Grade        |
| UPC                       | 783585435725          |

## Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type                 | RECEPTACLE               |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Weight Per each | 0.25 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Extra Heavy Duty Hospital Grade  |
| environmental conditions | Indoor Dry unless protected by additional means  |
| Mounting                 | Screw Mount  |
| nema rating              | 5-20R  |
| standard                 | CSA Certified, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA®<br>WD-6 Compliant;UL Listed to UL498 File No. E2186 |