



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948



JDL40 40A 600V Class J Time Delay Fuse

Edison Fuses

Catalog Number	JDL40
Manufacturer	Edison Fuses
Description	Eaton Edison Series JDL Fuse, Time-Delay Current-Limiting Fuse, Non-Indicating, 40 A, Class J, Non-Indicating, 200 Kaic, Standard, 10, 600 V
Weight per unit	0.1900 (lbs/each)
Product Category	Dual Element

Features

amperage rating	40
amps	40
dimensions	2.3800 IN X 1.0600 IN X 1.0600 IN
Fuse Class	Class J
Fuse Type	Class J Time Delay Fuses
interrupt rating	200 kAIC
media	Yes
Voltage	600V
Voltage Rating	600 V

Descriptions

Description	40A 600V CLASS J TIME DELAY FUSE
extra long description	MOR T626-JDL40 Class J Time Delay F
Features	Edison's UL Class J fuse products are offered in both Dual-Element Time-Delay (JDL) and Fast-Acting (JFL) types. Both types have 200,000 amp interrupting rating at 600Vac RMS Sym amps. Their small physical size and high performance characteristics makes Class J fuses ideal for any space-limited applications. Edison's JFL fuses are best suited for the protection of non-inductive loads such as resistive heating and lighting circuits.
Long Description	Eaton Edison series JDL fuse, Time-delay current-limiting fuse, Non-indicating, 40 A, Class J, Non-indicating, 200 kAIC, Standard, 10, 600 V
Product Type	Class J Time Delay Fuses 600V 40a
Special Features	Non-Indicating

Manufacturer Information

Brand	Eaton
GTIN	00782634803423
Manufacturers Part Number	JDL40
UPC	782634803423



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	1
Package	10
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Datacenters - Facilities: Critical Power
standard	UL Listed,CSA Certified,RoHS Compliant,CE Marked