



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 Heritage Parkway Suite 101
76063-0000, TX Mansfield
Phone: 682-518-7272
Fax: 682-518-7255



LMUC1002 24V 20MA Sensor *Wattstopper*

Catalog Number	LMUC1002
Manufacturer	Wattstopper
Description	<Div>The Lmuc-100 Low Profile Digital Ultrasonic Ceiling Mount Occupancy Sensor Uses Ultrasonic Diffusion Technology to Achieve 360° Occupancy Sensing For Energy-Efficient Control Of Lighting and Plug Loads. It Is A Digital Sensor, and Is Part Of A Wattstopper Digital Lighting Management (DLM) System.</Div>
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

included	Spring Clips
indicator	True
indoor/outdoor	Indoor
Input Voltage	24 VDC
Mounting Type	4 in Octagonal J-Box, Surface, Ceiling Tile
number of buttons	0.0
Number of Connections	2.0
Sensor Type	Occupancy
Voltage	24 VDC

Material, Color, and Finish

Finish	Glossy
--------	--------

Descriptions

Description	24V 20MA SENSOR
extra long description	WATT LMUC-100-2 Digital Ultrasonic
Features	Adjustable Time Delay, Load Controller Required, Indicator Lights, Sensitivity Adjustment
Long Description	<div>The LMUC-100 low profile Digital Ultrasonic Ceiling Mount Occupancy Sensor uses ultrasonic diffusion technology to achieve 360° occupancy sensing for energy-efficient control of lighting and plug loads. It is a digital sensor, and is part of a Wattstopper Digital Lighting Management (DLM) system.</div>
Product Type	Digital Ultrasonic Ceiling Mou NT Sensor, 1000 SQ FT

Manufacturer Information

Brand	Legrand-Wattstopper
GTIN	00754182926312
Manufacturers Part Number	LMUC1002
UPC	754182926312



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 Heritage Parkway Suite 101
76063-0000, TX Mansfield
Phone: 682-518-7272
Fax: 682-518-7255

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SENSOR

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

nema rating	WD 7
standard	ROHS, UL, cUL, FCC part 15, RoHS, PEP