



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948



NTC125 1-1/4" Rigid Threadless Raintight Connector

Appleton/Oz Gedney

Catalog Number	NTC125
Manufacturer	Appleton/Oz Gedney
Description	Compression Connector, Size: 1-1/4 In, Connection: Male Threaded X Compression, Material: Malleable Iron and Steel, Length: 1.94 In, Thread Length: 0.63 In, Diameter: 2.31 In, Standard: UI 514B, UI File Number E14814, Nema FB-1, For Use to Secure and Terminate Steel Emt to Knockouts and Concrete Tight Box
Weight per unit	0.6400 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded X Compression
Material	Malleable Iron And Steel

Dimensions and Weight

Size	1-1/4
------	-------

Descriptions

Description	1-1/4" RIGID THREADLESS RAIN TIGHT CONNECTOR
extra long description	APP NTC-125 1-1/4 IN CONN NO THRD R
Long Description	Compression Connector, Size: 1-1/4 IN, Connection: Male Threaded X Compression, Material: Malleable Iron And Steel, Length: 1.94 IN, Thread Length: 0.63 IN, Diameter: 2.31 IN, Standard: UL 514B, UL File Number E14814, NEMA FB-1, For Use To Secure And Terminate Steel EMT To Knockouts And Concrete Tight Box
Product Type	1-1/4 In Conn No THRD RGD Cond
Special Features	Concretetight

Manufacturer Information

Brand	Appleton
GTIN	00781381637855
Manufacturers Part Number	NTC-125
UPC	781381637855

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression Connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Packaging

Carton	5
Package	50
Weight Per each	0.64

Uses, Certifications, and Standards

Application	For Use To Secure And Terminate Steel EMT To Knockouts And Concrete Tight Box
standard	UL 514B, UL File Number E14814, NEMA FB-1