




GE  
Lighting

**68184 - LED26DP38S830/25**

GE LED PAR38

• Energy-efficient LED lamps. Long life.



**GENERAL CHARACTERISTICS**

Lamp Type	Replacement Lamps - Directional
Bulb	PAR38
Base	Medium Screw (E26)
Additional Info	Narrow Flood, 25o beam, Silver
Bulb Shape	PAR38
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	100.0 W
Lamp Type	LED-PAR
Life in Years (NOM)	22.8
Rated Life (MIN)	25000.0 h
Rated Life (NOM)	25000.0 h

**PHOTOMETRIC CHARACTERISTICS**

Beam Spread (NOM)	25.0 °
Center Beam Candlepower (CBCP) (NOM)	6800.0
Color Rendering Index (CRI) (NOM)	82.0
Color Temperature (NOM)	3000.0 K
Initial Lumens (TYP)	1500.0
Initial Lumens (NOM)	1500.0
Lumens per Watt (Efficacy) (NOM)	58.0 lm
Nominal Initial Lumens per Watt (NOM)	57.69231

**ELECTRICAL CHARACTERISTICS**

Estimated Energy Cost per Year (NOM)	3.13
Voltage (NOM)	120.0
Wattage (NOM)	26.0

**DIMENSIONS**

Bulb Diameter (DIA) (MIN)	4.750 in(120.6 mm)
Bulb Diameter (DIA) (NOM)	4.750 in(120.6 mm)
Maximum Overall Length (MOL) (NOM)	5.310 in(134.9 mm)

**PRODUCT INFORMATION**

Product Code	68184
Description	LED26DP38S830/25
Standard Package	00-Case
Standard Package GTIN	10043168681848
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168681841




GE  
Lighting

**68184 - LED26DP38S830/25**

GE LED PAR38

- Energy-efficient LED lamps. Long life.



**GENERAL CHARACTERISTICS**

Lamp Type	Replacement Lamps - Directional
Bulb	PAR38
Base	Medium Screw (E26)
Additional Info	Narrow Flood, 25o beam, Silver
Bulb Shape	PAR38
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	100.0 W
Lamp Type	LED-PAR
Life in Years (NOM)	22.8
Rated Life (MIN)	25000.0 h
Rated Life (NOM)	25000.0 h

**PHOTOMETRIC CHARACTERISTICS**

Beam Spread (NOM)	25.0 °
Center Beam Candlepower (CBCP) (NOM)	6800.0
Color Rendering Index (CRI) (NOM)	82.0
Color Temperature (NOM)	3000.0 K
Initial Lumens (TYP)	1500.0
Initial Lumens (NOM)	1500.0
Lumens per Watt (Efficacy) (NOM)	58.0 lm
Nominal Initial Lumens per Watt (NOM)	57.69231

**ELECTRICAL CHARACTERISTICS**

Estimated Energy Cost per Year (NOM)	3.13
Voltage (NOM)	120.0
Wattage (NOM)	26.0

**DIMENSIONS**

Bulb Diameter (DIA) (MIN)	4.750 in(120.6 mm)
Bulb Diameter (DIA) (NOM)	4.750 in(120.6 mm)
Maximum Overall Length (MOL) (NOM)	5.310 in(134.9 mm)

**PRODUCT INFORMATION**

Product Code	68184
Description	LED26DP38S830/25
Standard Package	00-Case
Standard Package GTIN	10043168681848
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168681841