



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596



PH50MQMJ 50 Va Mte CTRL XFRMR 240X480V-120X240V *Hammond Power Solutions*

Catalog Number	PH50MQMJ
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 50va
Weight per unit	N/A
Product Category	Encapsulated Industrial Contro

Features

Wattage	50
---------	----

Dimensions and Weight

Height	3.19
Length	4.38
Width	3.00

Descriptions

Description	50 VA MTE CTRL XFRMR 240X480V-120X240V
extra long description	HMND PH50MQMJ CNTL 50VA 240x480-120
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 50VA
Product Type	CNTL 50VA 240X480-120X240
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	HPS Imperator™
GTIN	00803423077938
Manufacturers Part Number	PH50MQMJ
UPC	803423077938

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10650 West Airport Suite 100
77477-0000, TX Stafford
Phone: 281-879-4911
Fax: 281-879-8596

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum