



Features

- Injection-molded thermoplastic ABS housing
- UL 94V-0 flame rating
- Innovative, snap-together design allows for fast installation
- Two fully adjustable glare-free round or eyeball shape light heads for emergency light
- Wall or ceiling mounting
- Easily removed mounting knock-outs and J-box pattern on back panel
- 120/277 VAC dual voltage operation
- Test switch and charge rate indicator
- 2 X 6V 5.4W DC T5 wedge or 2 X 6V 5W Halogen MR-16 lamps for emergency mode
- Battery delivers more than 90 minutes capacity to emergency lamps
- 24 hours recharge after 90 minutes discharge
- Low voltage battery disconnection preventing deep discharge damage to the battery
- Operating temperature range of 10°C to 40°C
- UL Listed for damp location
- Meets NFPA 101, NEC, and NEMA code



Dimensions



Accessories

Item #	Description
207WG	Wire Guard for Exit Sign
207WGWH	White Wire Guard for Exit Sign
207PS	Polycarbonate Shield for Exit Sign
20734J	Replacement Lead Acid Battery 6V 4.5Ah

Ordering Information

Catalog Model #	Description
20761	Emergency Light 2 x 5W MR16 Round Heads WH Finish
20763D	Emergency Light 2 x 5W MR16 Round Heads BLK Finish
20766SD	Emergency Light 2 x 5.4W Round Heads WH Finish with Self Diagnostics

