



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PJSE8W Duplex Receptacle Openings, End Sections, WH

Pass & Seymour/LeGrand

| | |
|------------------|--|
| Catalog Number | PJSE8W |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | <P>Sectional Wall Plate Semi-Jumbo Duplex End Section White</P> |
| Weight per unit | 0.0400 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|------------|
| cutout | Receptacle |
| insulation | Bare |
| Number of Gangs | 1 |

Dimensions and Weight

| | |
|-----------|--------|
| Size | 5.0 in |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--|
| Description | DUPLEX RECEPTACLE OPENINGS, END SECTIONS, WH |
| extra long description | P&S PJSE8W DISC SUB PJSE8WCC10 |
| Long Description | <p>Sectional Wall Plate Semi-Jumbo Duplex End Section White</p> |
| Product Type | Disc Sub Pjse8wcc10 |
| Special Features | Sectional wall plates to create your opening, molded of rugged thermoplastic |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007147025 |
| Manufacturers Part Number | PJSE8W |
| UPC | 785007147025 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | Residential plates |
| Type | Sectional wall plates |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.04 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CSA, UL, UL 514 |