



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120  
75041-0000, TX Garland  
Phone: 214-503-7227  
Fax: 214-503-9766



## LL50DCG 1/2" LL Alu FM5 Condulet W/C&G *Appleton/Oz Gedney*

Catalog Number	LL50DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Series: LL, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Finish, Gasket: Neoprene, UI Standard: 514A, Trade Size: 1/2
Weight per unit	0.3000 (lbs/each)
Product Category	Alum

### Features

Material	Die Cast Aluminum
----------	-------------------

### Material, Color, and Finish

Finish	Epoxy Powder Coat;Other
--------	-------------------------

### Dimensions and Weight

Height	1.64
Hub Size	1/2
Length	4.4
Width	2.06

### Descriptions

Description	1/2" LL ALU FM5 CONDULET W/C&G
extra long description	EGS LL50DCG 1/2 IN THD ALUM LL BDY
Long Description	EMT Conduit Bodies, Aluminum Threaded for rigid conduit and IMC, Series: LL, Material: Conduit Body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural finish, Gasket: neoprene, UL Standard: 514A, Trade Size: 1/2
Product Type	1/2 In THD Alum LL Bdy CVR
Special Features	1/2 IN Trade Size, Type LL Aluminum Threaded Conduit Body, Volume 4.35 IN <sup>3</sup> , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

### Manufacturer Information

Brand	Appleton
GTIN	00687855000685
Manufacturers Part Number	LL50DCG
UPC	687855000685



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120  
75041-0000, TX Garland  
Phone: 214-503-7227  
Fax: 214-503-9766

## Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body

## Packaging

Carton	10
Package	50
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A