# Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685




## LMSW105W Scene Switch

*Wattstopper*

| | |
|---|---|
| Catalog Number | LMSW105W |
| Manufacturer | Wattstopper |
| Description | Watt LMSW-105-W Digital Scene Switc |
| Weight per unit | 2.9 (lbs/each) |
| Product Category | Lighting Controls |

### Features

| | |
|---|---|
| indoor/outdoor | Indoor |
| Input Voltage | 24 VDC |
| Material | ABS |
| Mounting Type | J-Box |
| number of buttons | 5.0 |
| Number of Connections | 2.0 |
| Number of Switches | 5.0 |
| Switch Type | Push |

### Material, Color, and Finish

| | |
|---|---|
| Color | White |
| Finish | Glossy |

### Descriptions

| | |
|---|---|
| Description | SCENE SWITCH |
| Features | The LMSW-105 Digital Scene Switch is a low voltage device that sets and recalls preset lighting scenes and raises and lowers lighting levels. It is part of a Digital Lighting Management (DLM) system and controls loads connected to DLM room controllers by accessing four of the 16 scenes available in a DLM local network. |
| Long Description | WATT LMSW-105-W Digital Scene Switc |
| Product Type | Digital Scene Switch, 5-Button |

### Manufacturer Information

| | |
|---|---|
| Brand | Legrand-Wattstopper |
| GTIN | 00754182929283 |
| Manufacturers Part Number | LMSW105W |
| UPC | 754182929283 |

### Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Residential Switches |
| Type | SWITCH |

### Trade Size

| | |
|---|---|
| Amperage | 5.0 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Availability

| | |
|---|---|
| Manufacturer Status | Inactive |

## Packaging

| | |
|---|---|
| Carton | 10 |
| Package | 40 |
| Weight Per each | 2.9 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Operating Temperature | 0°-55°C, 32°-131°F |
| standard | ROHS, UL, FCC part 15, RoHS, cUL |