



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

405 Technology Drive
78602-0000, TX Bastrop
Phone: 512-772-2493
Fax: 512-772-2494



LT38 3/8" STR LT Steel Conn

Crouse-Hinds

Catalog Number	LT38
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Liquidator Liquidtight Connector, FMC, Straight, Non-Insulated, Malleable Iron, 3/8"
Weight per unit	0.1600 (lbs/each)
Product Category	Liquid Tight Fittings

Features

connection	Threaded
dimensions	1.6300 IN X 1.1300 IN X 1.1300 IN
installation type	THREADED

Material, Color, and Finish

Color	MALLEABLE IRON
-------	----------------

Descriptions

Description	3/8" STR LT STEEL CONN
extra long description	MIDWEST LT38 3/8 LT CONN
Features	Liquidtight fittings from Eaton's Crouse-Hinds Division are designed to protect conductors from mechanical damage due to vibration and movement while sealing out cutting oils, coolants, water, and dust. Typical applications include the wiring of machine tools, motors, transformers, food processing equipment, robotics, air conditioning units and illuminated signs. To meet any customer preference, Crouse-Hinds series liquidtight fittings are available in a variety sizes, configurations and materials, inclu
Long Description	Eaton Crouse-Hinds series Liquidator liquidtight connector, FMC, Straight, Non-insulated, Malleable iron, 3/8"
Product Type	3/8 LT Conn

Manufacturer Information

Brand	Eaton
GTIN	00784564300386
Manufacturers Part Number	LT38
UPC	784564300386

Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Liquidtight connector

Trade Size

Trade Size	3/8 in
------------	--------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

405 Technology Drive
78602-0000, TX Bastrop
Phone: 512-772-2493
Fax: 512-772-2494

Packaging

Carton	25
Weight Per each	0.16

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 467, UL 514B, CSA C22.2