



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MDL10 10A 32V TD Glass Fuse

Bussmann Fuses

| | |
|------------------|------------------------------------|
| Catalog Number | MDL10 |
| Manufacturer | Bussmann Fuses |
| Description | Buss MDL-10 1/4 X 1-1/4 Time Delay |
| Weight per unit | 0.0070 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|--------------------|---|
| amperage rating | 10 Amp |
| connection | Ferrule End X Ferrule End |
| Response Time | 60 Min Maximum at 135%, 120 S Maximum at 200% |
| type of indicators | Non-Indicating |
| Voltage Rating | 32 VAC |

Dimensions and Weight

| | |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|

Descriptions

| | |
|------------------|--|
| Description | 10A 32V TD GLASS FUSE |
| Long Description | BUSS MDL-10 1/4 X 1-1/4 TIME DELAY |
| Product Type | 1/4 X 1-1/4 Time Delay Glass - 10 Amp |
| Special Features | Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap |

Manufacturer Information

| | |
|---------------------------|-------------------------------|
| Brand | Cooper Bussmann North America |
| GTIN | 00051712724579 |
| Manufacturers Part Number | MDL-10 |
| UPC | 051712724579 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Electronic, Time Delay |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status | Inactive |

Packaging

| | |
|-----------------|-------|
| Carton | 5 |
| Weight Per each | 0.007 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Electronic Circuits

standard

UL 248-14, CSA, CE