



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3130 S Dodge Boulevard  
85713-0000, AZ Tucson  
Phone: 520-526-1947  
Fax: 520-526-1948



## NTC125 1-1/4" Rigid Threadless Raintight Connector

*Appleton/Oz Gedney*

Catalog Number	NTC125
Manufacturer	Appleton/Oz Gedney
Description	Compression Connector, Size: 1-1/4 In, Connection: Male Threaded X Compression, Material: Malleable Iron and Steel, Length: 1.94 In, Thread Length: 0.63 In, Diameter: 2.31 In, Standard: UI 514B, UI File Number E14814, Nema FB-1, For Use to Secure and Terminate Steel Emt to Knockouts and Concrete Tight Box
Weight per unit	0.6400 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Male Threaded X Compression
Material	Malleable Iron And Steel

### Dimensions and Weight

Size	1-1/4
------	-------

### Descriptions

Description	1-1/4" RIGID THREADLESS RAIN TIGHT CONNECTOR
extra long description	APP NTC-125 1-1/4 IN CONN NO THRD R
Long Description	Compression Connector, Size: 1-1/4 IN, Connection: Male Threaded X Compression, Material: Malleable Iron And Steel, Length: 1.94 IN, Thread Length: 0.63 IN, Diameter: 2.31 IN, Standard: UL 514B, UL File Number E14814, NEMA FB-1, For Use To Secure And Terminate Steel EMT To Knockouts And Concrete Tight Box
Product Type	1-1/4 In Conn No THRD RGD Cond
Special Features	Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00781381637855
Manufacturers Part Number	NTC-125
UPC	781381637855

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3130 S Dodge Boulevard  
85713-0000, AZ Tucson  
Phone: 520-526-1947  
Fax: 520-526-1948

## Packaging

Carton	5
Package	50
Weight Per each	0.64

## Uses, Certifications, and Standards

Application	For Use To Secure And Terminate Steel EMT To Knockouts And Concrete Tight Box
standard	UL 514B, UL File Number E14814, NEMA FB-1