



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PRL1A1600X42C PRL1A Interior For TFL 120/240V 1PH 3W 600A 42 CKT *Eaton Corp*

Catalog Number	PRL1A1600X42C
Manufacturer	Eaton Corp
Description	Eaton Pow-R-Stock PRL1A Panelboard, Interior, 208Y/120V, Single-Phase, 4W, 600A, Copper Bus, 42 Circuit
Weight per unit	60.0 (lbs/each)
Product Category	20151105172103

Features

amperage rating	600A
dimensions	67.0000 IN X 18.0000 IN X 7.0000 IN
media	Yes
Phase	Single-phase
Short Circuit Rating	35
Voltage Rating	240V

Descriptions

Also Known As...	load center panel board panel Fuse box electric panel breaker panel breaker box panelboard
Description	PRL1A INTERIOR FOR TFL 120/240V 1PH 3W 600A 42 CKT
extra long description	ETN PRL1A1600X42C 208Y/120V, 1PH, 4
Features	Panelboards Pow-R-Stock Plus Program provide interiors; type 1 and 3R boxes; surface and flush trims; factory-assembled panelboards; main breaker kits; branch breakers; lug kits; service entrance kits; ground kits; and 200% neutral kits. In addition, the distributor stocking program can be used with various Eaton commercial distribution products and is designed to meet UL67 standards for use in data center, industrial, commercial and healthcare facilities.
Long Description	Eaton Pow-R-Stock PRL1A panelboard, Interior, 208Y/120V, Single-phase, 4W, 600A, Copper bus, 42 circuit
Product Type	208Y/120V, 1PH, 4W, 600A, 42 Circuit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786687010739
Manufacturers Part Number	PRL1A1600X42C
UPC	786687010739

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BOXES & INTERIORS
Type	PRL1A Panelboard

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	60

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
Operating Temperature standard	40°C UL 67,NEMA Compliant