



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1200 Water St  
78028-0000, TX Kerrville  
Phone: 830-896-9240  
Fax: 830-896-9244



## PS30AC2W 30A 120/277VAC B+S Wire DP SW WH

*Pass & Seymour/Legrand*

Catalog Number	PS30AC2W
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 2 Poles, 30 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, White, Grounding Connection, Wall Mount, 1.437 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.23 LB
Weight per unit	0.2281 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Double pole
actuator	Toggle
amperage rating	30
Contact Rating	30Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	30 A @ 120/277 VAC
Load Type	Fluorescent, Halogen, LED, Universal, Incandescent, CFL, Xenon
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	120/277 V
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	30A 120/277VAC B+S WIRE DP SW WH
extra long description	P&S PS30AC2W 30A 120/277VAC B+S WIR

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195569
Manufacturers Part Number	PS30AC2W
UPC	785007195569



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1200 Water St  
78028-0000, TX Kerrville  
Phone: 830-896-9240  
Fax: 830-896-9244

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

## Trade Size

Amperage	30.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.2281

## Uses, Certifications, and Standards

Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC