



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT2097HGW Self Test Plugtail Gfci Recp Hosp GRD 20A WH

Pass & Seymour/Legrand

Catalog Number	PT2097HGW
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Plugtail Self Test Hospital Grade Gfci White
Weight per unit	0.2450 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Built-in Connector
interrupt rating	4 to 6 mA
Material	Thermoplastic
media	Yes
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73

Descriptions

Description	SELF TEST PLUGTAIL GFCI RECP HOSP GRD 20A WH
extra long description	P&S PT2097HGW SLF TST PLUGTAIL GFCI
Long Description	20A 125V Plugtail Self Test Hospital Grade GFCI White
Product Type	SLF TST Plugtail Gfci HS GRD Rec 20A W
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007048223
Manufacturers Part Number	PT2097HGW
UPC	785007048223



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	PLUGTAIL® Hospital Grade Tamper-Resistant 20A Self-Test GFCI Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.245

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL