



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## T2535183S 25KVA 1PH 480/240 Dry Type Transformer

Acme Electric

Catalog Number	T2535183S
Manufacturer	Acme Electric
Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kva
Weight per unit	260.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

### Features

Fuse Rating	Primary: 150 AMP For 240 V, 70 AMP For 480 V, Secondary: 300 AMP For 120 V
pallet quantity	4
Primary Voltage	240 X 480
product category	Dry Type Distribution Transformer
Secondary Voltage	120/240

### Dimensions and Weight

Height	18.44
Length	13.34
Width	16.13

### Descriptions

Construction	ENCAPSULATED
Description	25KVA 1PH 480/240 DRY TYPE TRANSFORMER
extra long description	ACME T2535183S TFMR 1PH 25KVA 240X4
Long Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kVA
Product Type	Dry Type Distribution Transformer
Special Features	Encapsulated core and coil; Shielded for cleaner power; Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air, UL type 3R enclosure for indoor or outdoor service, encapsulation eliminates corrosion and insulation deterioration; Quiet operation with sound levels well below NEMA standards; 10-year limited warranty

### Manufacturer Information

Brand	ACME ELECTRIC
GTIN	00047503734209
Manufacturers Part Number	T2535183S
UPC	047503734209



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description 1 PHASE TRANSFORMERS

Type Distribution Transformer

## Packaging

Carton 1

Weight Per each 260

## Uses, Certifications, and Standards

Enclosure NEMA 3R Steel

Mounting WALL

standard UL 506, UL File Number E79947V1, UL Control Number 50B8, UL  
Insulation Number H3221, CSA Certified, OSHA Compliant, ANSI,  
IEEE

Temperature Rating 115 DEG C Rise