


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	ENGLISH	METRIC	L ± .03 [0,51]	W ± .01 [0,25]	C ± .02 [0,38]	M ± .03 [0,51]	H ± .01 [0,25]
PV10-6F	#6	M3,5	1.01 [25,7]	.31 [7,9]	.25 [6,4]	.81 [20,6]	.14 [3,6]
PV10-8F	#8	M4	1.04 [26,4]	.37 [9,4]	.25 [6,4]	.81 [20,6]	.17 [4,3]
PV10-10F	#10	--	1.04 [26,4]	.37 [9,4]	.25 [6,4]	.81 [20,6]	.20 [5,1]
PMV6-5F	--	M5	1.04 [26,4]	.38 [9,7]	.22 [6,0]	.81 [20,6]	.21 [5,3]
PV10-14F	1/4"	M6	1.14 [29,0]	.49 [12,5]	.32 [8,1]	.88 [22,4]	.26 [6,6]

UL & CSA APPROVED TOOLS

CT-100B - #16-14 AWG
 CT-1550 - #18-14 AWG
 CT-1551 - #18-14 AWG
 CT-2300 - #18-14 AWG
 CT-2500 (CT-2550CH) - #14-10 AWG

METRIC EQUIVALENT
 #14 AWG = 2,5mm
 #12 AWG = 4,0 mm
 #10 AWG = 6,0 mm



NOTES:

- UL 486A/B LISTED & CSA C22.2 NO. 65-03 CERTIFIED FOR:
 - SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600V. MAX. BLDG WIRE.
(1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
 - SOME TOOLS HAVE EXPANDED WIRE SIZES. SEE TOOL TABLES FOR AWG WIRE SIZES SUPPORTED BY EACH TOOL.
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES.
- MATERIAL:
 - STAMPING: .04" [1,0] THK COPPER, TIN PLATED
 - HOUSING: VINYL, YELLOW
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT.
- WIRE STRIP LENGTH: 5/16 ^{+1/32}₋₀ [7,9 ^{+0,8}₋₀]



PART NUMBER		SEE TABLE	
TITLE			
FORK TERMINAL, 2 Pc. VINYL INSULATED, #12-10.			
CUSTOMER DRAWING			
ITEM REVISION NAME		N41189BA/07	
DATASET FILE NAME		N41189BA-DC r07A	
MATERIAL		SEE NOTE 3	
DRAWING NUMBER		A41189	
DRAWN BY	DATE	CHK	SCALE
DFTR	-	FS	N.T.S.
SHEET 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
07A	08-08-24	DPOI	ACC	GSI	UPDATED TITTLE BLOCK, MODIFY NOTES, ADD NEW UL LOGO, ADD TOOL CHART & METRIC EQUIVALENTS.	005643/00
05A	07-07-14	MBY	JHNU	RGB	JHNU RGB REVISED NOTES, MOVED TOOLS TO TABLE, REVISED CERTIFICATION	-
04	07-12-12	BDK	LCA	VMB	ADDED PMV6-5F. ADDED METRIC EQUIVALENT. CHANGE PACKAGING NOTE. REVISED INSTALLATION TOOLS NOTE. BROUGHT DRAWING TO CURRENT STANDARDS.	-

A-SIZE CUSTOMER